



Product Service

CERTIFICATE

No. Z1A 057396 1088 Rev. 00

Holder of Certificate: **XP Power LLC.**
340 Commerce, Suite 100
Irvine CA 92602
USA

Certification Mark:



Product: **Adaptors**
(SWITCHING POWER ADAPTOR)

Tested according to: EN IEC 62368-1:2020/A11:2020
AfPS GS 2019:01 PAK

With this certificate, in its capacity as a notified GS body, TÜV SÜD Product Service GmbH issues the GS Mark to the named certificate holder for the declared product with the named model designation in accordance with section 20 ProdSG (German Product Safety Act). The product meets the safety and health requirements of section 20 (3) ProdSG. The manufacturer is reminded of their obligations in accordance with section 24 ProdSG. The certification marks shown above can be affixed on the product. It is not permitted to alter the certification marks in any way. In addition, the certificate holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 652102536301A

Valid until: 2030-12-17

Date, 2026-01-05

(Rickyet Wang)

CERTIFICATE

No. Z1A 057396 1088 Rev. 00

Model(s):

AUM90PSXXX-C6YYYYYYYY, AUM90PSXXXYYYYYYYY, AUM90PSXX-C6YYYYYYYY, AUM90PSXXYYYYYYYY (XXX=110-120 or 140-190 or 210-300 or 320-400 or 421-430 or 451-460 or 471-480 or 511-520 or 531-540, indicates the rated output voltage range from 11.0VDC to 12.0VDC or 14.0VDC to 19.0VDC or 21.0VDC to 30.0VDC or 32.0VDC to 40.0VDC or 42.1VDC to 43.0VDC or 45.1VDC to 46.0VDC or 47.1VDC to 48.0VDC or 51.1VDC to 52.0VDC or 53.1VDC to 54.0VDC, and rises by step of 0.1VDC; XX=11-12 or 14-19 or 21-30 or 32-38 or 40 or 43 or 46 or 48 or 52 or 54, indicates the rated output voltage range from 11.0VDC to 12.0VDC or 14.0VDC to 19.0VDC or 21.0VDC to 30.0VDC or 32.0VDC to 38.0VDC or 40.0VDC or 43.0VDC or 46.0VDC or 48.0VDC or 52.0VDC or 54.0VDC, and rises by step of 1.0VDC; Y=0-9, a-z, blank or dash symbol '-', only for marketing purposes, no safety impact)

Brand Name:

XP Power

**Parameters:**

Rated Input: 100-240VAC, 50/60Hz or 50-60Hz, 1.5A Max.

Rated Output: See below table for details

Protection Class: I

Degree of Protection: IP20

CERTIFICATE

No. Z1A 057396 1088 Rev. 00

Model	Rated output voltage (VDC)	Rated output current (A)	Max. rated output power (W)
AUM90PSXXX-C6YYYYYYYYY, AUM90PSXXXYYYYYYYYY, AUM90PSXX-C6YYYYYYYYY, AUM90PSXXYYYYYYYYY	11.0-12.0	7.00	84.0
	14.0-15.0	6.00	90.0
	15.1-16.0	5.62	89.92
	16.1-17.0	5.29	89.93
	17.1-18.0	5.00	90.0
	18.1-19.0	4.73	89.87
	21.0-22.0	4.09	89.98
	22.1-23.0	3.91	89.93
	23.1-24.0	3.75	90.0
	24.1-25.0	3.60	90.0
	25.1-26.0	3.46	89.96
	26.1-27.0	3.33	89.91
	27.1-28.0	3.21	89.88
	28.1-29.0	3.10	89.90
	29.1-30.0	3.00	90.0
	32.0-33.0	2.72	89.76
	33.1-34.0	2.64	89.76
	34.1-35.0	2.57	89.95
	35.1-36.0	2.50	90.0
	36.1-37.0	2.43	89.91
	37.1-38.0	2.36	89.68
	39.1-40.0	2.25	90.0
42.1-43.0	2.09	89.87	
45.1-46.0	1.95	89.70	
47.1-48.0	1.87	89.76	
51.1-52.0	1.73	89.96	
53.1-54.0	1.67	90.18	