



Product Service

CERTIFICATE

No. B 057396 0602 Rev. 00

Model(s):

HPT5K0TSxxx-L Series (where x can be 0 to 9 which represents rated output voltage)

Brand Name:

XP

Parameters:

Input Voltage: 200-240 VAC or 380-480 VAC, 3-Phase (3W+PE)
 Input Frequency: 50/60 Hz
 Input Current: 10 A Max Per Phase
 Protection Class: Class I at end use
 Max Temperature, ambient: 50°C with 100% rated output;
 70°C with 50% rated output
 Elevation for use: 0-5000 m above sea level

Approved models and Rated Outputs:

Model Number	OUTPUT RATING				
	Voltage (VDC)	200-240 V ac input range		380-480 Vac input range	
		Max Current (A)	Max Power (W)	Max Current (A)	Max Power (W)
HPT5K0TS048-L	0-48 (0-50.4)	62.5	3000	104.17	5000
HPT5K0TS060-L	0-60 (0-63)	50	3000	83.33	5000
HPT5K0TS100-L	0-100 (0-105)	30	3000	50	5000
HPT5K0TS200-L	0-200 (0-210)	15	3000	25	5000

TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD
 ZERTIFIKAT ◆ CERTIFICATE ◆ 認證證書 ◆ CERTIFICADO ◆ CERTIFICAT



164 / 07.17

