



Product Service

# CERTIFICATE

No. B 057396 0648 Rev. 00

**Holder of Certificate:** **XP Power LLC.**

15641 Red Hill Avenue, Suite 100  
Tustin CA 92780  
USA

**Certification Mark:**



**Product:**

**AC-DC and DC-DC converters  
(AC-DC converter)**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the testing and certification regulations of TÜV SÜD Group have to be complied. For details see: [www.tuvsud.com/ps-cert](http://www.tuvsud.com/ps-cert)

**Test report no.:** 64210210090401A

**Valid until:** 2026-05-12

**Date,** 2021-05-26

( Richard Zhu )

# CERTIFICATE

No. B 057396 0648 Rev. 00

**Model(s):**

LCW15US03, LCW15US03-E, LCW15US03-x,  
 LCW15US03-E-x, LCW15US03-xx, LCW15US03-E-xx,  
 LCW15US03-xxx, LCW15US03-E-xxx, LCW15US05,  
 LCW15US05-E, LCW15US05-x, LCW15US05-E-x,  
 LCW15US05-xx, LCW15US05-E-xx, LCW15US05-xxx,  
 LCW15US05-E-xxx, LCW15US12, LCW15US12-E,  
 LCW15US12-x, LCW15US12-E-x, LCW15US12-xx,  
 LCW15US12-E-xx, LCW15US12-xxx, LCW15US12-E-xxx,  
 LCW15US15, LCW15US15-E, LCW15US15-x,  
 LCW15US15-E-x, LCW15US15-xx, LCW15US15-E-xx,  
 LCW15US15-xxx, LCW15US15-E-xxx, LCW15US24,  
 LCW15US24-E, LCW15US24-x, LCW15US24-E-x,  
 LCW15US24-xx, LCW15US24-E-xx, LCW15US24-xxx,  
 LCW15US24-E-xxx, LCW15US48, LCW15US48-E,  
 LCW15US48-x, LCW15US48-E-x, LCW15US48-xx,  
 LCW15US48-E-xx, LCW15US48-xxx, LCW15US48-E-xxx  
 (x=0-9, A-Z stands for different marketing purpose.)

**Brand Name:**

**XP Power**



**Parameters:**

Rated Input: 100-240VAC, 0.4A, 50/60Hz  
 Rated Output: See below table for details  
 Protection Class: I  
 Degree of Protection: IPX0

**Remark:**

- The products are built-in type equipment, suitable enclosure should be provided by end system.

**Tested according to:** EN 62368-1:2014/A11:2017

# CERTIFICATE

No. B 057396 0648 Rev. 00

Model number	Output voltag(VDC)	Output current (A)	Output power
LCW15US03 , LCW15US03-E , LCW15US03-x , LCW15US03-E-x , LCW15US03-xx , LCW15US03-E-xx , LCW15US03-xxx , LCW15US03-E-xxx	3.3V	3.0A	9.9W
LCW15US05 , LCW15US05-E , LCW15US05-x , LCW15US05-E-x , LCW15US05-xx , LCW15US05-E-xx , LCW15US05-xxx , LCW15US05-E-xxx	5.0V	3.0A	15.0W
LCW15US12 , LCW15US12-E , LCW15US12-x , LCW15US12-E-x , LCW15US12-xx , LCW15US12-E-xx , LCW15US12-xxx , LCW15US12-E-xxx	12.0V	1.3A	15.6W
LCW15US15 , LCW15US15-E , LCW15US15-x , LCW15US15-E-x , LCW15US15-xx , LCW15US15-E-xx , LCW15US15-xxx , LCW15US15-E-xxx	15.0V	1.0A	15.0W
LCW15US24 , LCW15US24-E , LCW15US24-x , LCW15US24-E-x , LCW15US24-xx , LCW15US24-E-xx , LCW15US24-xxx , LCW15US24-E-xxx	24.0V	0.625A	15.0W
LCW15US48 , LCW15US48-E , LCW15US48-x , LCW15US48-E-x , LCW15US48-xx , LCW15US48-E-xx , LCW15US48-xxx , LCW15US48-E-xxx	48.0V	0.32A	15.36W