



Ref. Certif. No.

**DK-163176-UL**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

DC to DC Converter

Name and address of the applicant

XP POWER LLC  
340 COMMERCE, SUITE 100 IRVINE, CA 92602  
United States

Name and address of the manufacturer

XP POWER LLC  
340 COMMERCE, SUITE 100 IRVINE, CA 92602  
United States

Name and address of the factory

No 133 Lide Rd Daliao District Kaohsiung City, 831  
TAIWAN

Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

(Optional) Input: 2.97-3.63 or 3.3.  
See test report for details.

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

#SDT01Fxyz#, #SDT01F03V3D3V3#, #SDT01F03V3D05#,  
#SDT01F03V3D09#, #SDT01F03V3D12#, #SDT01F03V3D15#  
☒ Additional Information on page 2

Additional information (if necessary may also be reported on page 2)

National Differences: AU, CA, CN, EU Group Differences, JP, NZ, SA, GB, US  
☒ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2018

As shown in the Test Report Ref. No. which forms part of this Certificate

2501047-CB issued on 2025-02-18

This CB Test Certificate is issued by the National Certification Body



☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA  
☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK  
☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN  
☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2025-02-21

Signature:

Thomas Wilson



Ref. Certif. No.

**DK-163176-UL**

**Additional Model Detail(s):**

#SDT01Fxyz#, #SDT01F03V3D3V3#, #SDT01F03V3D05#, #SDT01F03V3D09#, #SDT01F03V3D12#, #SDT01F03V3D15#,  
x can be 03, 05, 12, or 24 for input voltage.

y can be S, D.

z can be 3V3, 05, 05, 09, 09, 12, 12, 15 or 15 for output voltage.

"#" can be any alphanumeric characteristic, punctuation mark or blank.

**Additionally evaluated to:**

EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020

**Additional information (if necessary)**



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2025-02-21

Signature:

Thomas Wilson