



CERTIFICATE

No. B 057396 0353 Rev. 01

Holder of Certificate: **XP Power LLC.**
15641 Red Hill Avenue, Suite 100
Tustin CA 92780
USA

Certification Mark:



Product: Power supply

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

Test report no.: 095-72143850F-000

Valid until: 2024-05-30

Date, 2019-06-21

(Adrian Rabago Valenzuela)



Product Service

CERTIFICATE

No. B 057396 0353 Rev. 01

Model(s):

ECS65USxx

(where xx can be number 12 to 48 to indicate the main output voltage, may be also followed by suffix "SF" and/or "-B")

Brand Name:

XP



Parameters:

Rated Input Voltage: 100-240 VAC

Rated Input Current: 1.2 A

Rated Input Frequency: 50/60 Hz (all models)

50/60/400 Hz (optional for ECS65US12)

Protection Class: Class I or Class II at end use

Temperature, Ambient: 50°C with 100% rated output

70°C with 50% rated output

Elevation for use: 0-5000 m above sea level

Approved models and Rated Outputs:

Model Number	OUTPUT RATING		
	Voltage (VDC)	Current (A)	Max. Power (W)
ECS65US12	10.1 to 13.5	5.4	65
ECS65US15	13.6 to 17	4.3	65
ECS65US18	17.1 to 21	3.6	65
ECS65US24	21.1 to 26	2.7	65
ECS65US28	26.1 to 31	2.3	65
ECS65US33	31.1 to 33	2.0	65
ECS65US36	33.1 to 42	1.8	65
ECS65US48	42.1 to 54	1.35	65

Suffix:

"-SF": single fuse is provided in the line side of primary

"-B": unit is provided with additional EMI filter inductor (L2)



Product Service

CERTIFICATE

No. B 057396 0353 Rev. 01

Conditions of Acceptability:

When installing the equipment, all requirements of the standards and the manufacturer's specifications must be met.

The models require:

- A suitable electrical and fire enclosure must be provided in the end use equipment.
 - The product is intended for use on the following power system: TN
 - The following output circuits are at ES1 energy levels: All.
 - The following output circuits are at PS2 energy levels: All.
 - The following input terminals/connectors must be connected to the end-product supply neutral: CAN J1.
 - A suitable main disconnect device shall be provided in the end product.
 - When installed in end product, sufficient clearance and creepage distance shall be provided between the primary circuit and accessible conductive parts.
 - Proper bonding to the end-product main protective earthing terminal is required when installed in Class I end product, ground bond test shall be conducted.
 - Touch current test and dielectric Strength test need to be considered at end use equipment.
 - Heatsinks are floating and considered live, they shall not be accessible in the end product.
 - Power supplies without suffix "-SF" have a fuse in the neutral of the primary circuit.
- Additional warnings to be considered in the end product.

Tested according to: EN 62368-1:2014/A11:2017

Production Facility(ies): 071712, 089850, 059061, 059319