



Product Service

CERTIFICATE

No. B 057396 0863 Rev. 01

Holder of Certificate: **XP Power LLC.**
340 Commerce, Suite 100
Irvine CA 92602
USA

Certification Mark:



Product: **Switching power supply unit**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 7191302260-09-TR

Valid until: 2026-01-07

Date, 2024-07-23

(Kim Hock Teo)

CERTIFICATE

No. B 057396 0863 Rev. 01

Model(s):

SHP650PSxx-yy

Where xx is between 12-48 representing designated output.
-yy is -EF, for model with top cover with fan at the end of the power supply chassis, or -TF for model with top cover with fan at the top of the power supply chassis, or blank for model without top cover and fan.

Brand Name:

XP

Parameters:

Rated Input: 100-240 VAC, 50/60 Hz, 9.0 A or
100-120 VAC, 400 Hz, 9.0 A (only available for 12 V output variant)
Protection Class: Class I at end use
Elevation for use: 0-5000m above sea level
Temperature, Ambient: 50°C with 100% load
70°C with 50% load

The product is a component AC-DC power supply for building-in, open frame type provided with a metal chassis intended for Class I end-product application.

Output Rating

Model Number	OUTPUT RATING @ 50°C AMBIENT			OUTPUT RATING @ 70°C AMBIENT		
	Voltage (VDC)	Max Current (A)	Max Power (W)	Voltage (VDC)	Max Current (A)	Max Power (W)
SHP650PS12	12.0	50	607	12.0	25	300
SHP650PS15	15.0	40	607	15.0	20	300
SHP650PS24	24.0	27	657	24.0	13.5	324
SHP650PS28	28.0	23	651	28.0	11.5	322
SHP650PS36	36.0	18	657	36.0	9.0	324
SHP650PS48	48.0	13.5	657	48.0	6.75	324
Models provided with the following -yy values differ as follows: -EF: Provided with top cover with fan located at the end of the power supply chassis -TF: Provided with top cover with fan located at the top of the power supply chassis Blank: Not provided with top cover and no fan, only provided with U-shaped chassis						

CERTIFICATE

No. B 057396 0863 Rev. 01

Conditions of Acceptability:

When installing the equipment, all requirements of the standards and the manufacturer's specifications must be met.

The models require:

- The following output circuits are at ES1 energy levels: All Outputs
- The following output circuits are at PS3 energy levels: All Outputs
- The product is intended for use on the following power systems: TN
- The maximum investigated branch circuit rating is: 20 A
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required (Class I)
- The following input terminals/connectors must be connected to the end-product supply neutral: AC N
- The following end-product enclosures are required: Mechanical, Fire, Electrical
- When installed in a Class I end product, the power supply shall be mounted in a manner that provides the minimum required Clearance between the primary side of power supply and protectively earthed accessible conductive parts.
- Heatsinks are floating and considered live. They should not be accessible in the end-product.
- A suitable main disconnect device shall be provided in the end product.

Tested according to: EN 62368-1:2014/A11:2017