

Date : 22.12.2020

XP Power Limited
401 Commonwealth Drive
Haw Par Technocentre, Lobby B,
#02-02 149598
Singapore
Attn:

Re. : CU US + Canada Certificate

Type of Equipment : DIN RAIL MOUNTABLE POWER SUPPLIES
Model Designation : See Certificate
Certificate No. : CU 72205400 0001
File No. : 50429506 003
Engineer/Contact : Andreas Klinker
Standard(s) : UL 62368-1:2014
CAN/CSA-C22.2 NO. 62368-1-14

Dear Madame or Sir,

The above referenced technical equipment has been tested and was found to be in compliance with the listed test requirement(s). Enclosed, please find the TUV Rheinland approval document No. CU 72205400 0001. It authorizes you to label the listed product(s) with the TUV Rheinland Mark identified in the approval document. For compliance, the Test Mark must be on the approved unit.

Your product is subject to regular factory follow-up inspections as well as annual certificate and factory registration fees.

In using the TUV Rheinland Mark you are obligated to comply with the TUV Rheinland of North America Service Agreement.

If we can be of any further assistance to you, please do not hesitate to contact us.

Sincerely yours,
Certification Body



Dipl.-Ing. A. Klinker
QA Certification Officer

Enclosure

Certificate



Certificate no.

CU 72205400 01

License Holder:

XP Power Limited
401 Commonwealth Drive
Haw Par Technocentre, Lobby B,
#02-02 149598
Singapore

Manufacturing Plant:

-AK-50429506 001

Test report no.: USA-AK 50429506 003

Client Reference: N/A

Tested to:

UL 62368-1:2014
CAN/CSA-C22.2 NO. 62368-1-14

Certified Product: DIN RAIL MOUNTABLE POWER SUPPLIES

License Fee - Units

Model Designation: 1) DNR240TS24-I; 2) DNR240TS48-I
(trademark: XP)

4

Rated Voltage : 3PH 400-500 Vac, 47-63Hz

Rated Current : 0.85A


Output Ratings : 1) DC 24V, 10A, 240W;
2) DC 48V, 5A, 240W

Protection Class : I

Rated Ambient Temperature: 50°C

4

Licensed Test mark:



Date of Issue
(day/mo/yr)

22/12/2020