



Product Service

CERTIFICATE

No. B 057396 0348 Rev. 01

Output Power under different configurations:

Model Number	Convectional Cooling Without Cover		Convectional Cooling With Cover		Forced Air Cooling With Cover	
	Max Output @50°C	Max Output @70°C	Max Output @50°C	Max Output @70°C	Max Output @50°C	Max Output @70°C
GCS250PS12	180W, 15A	90W, 7.5A	145W, 12.1A	72.5W, 6.04A	225W, 18.7A	112.5W, 9.38A
GCS250PS15	180W, 13A	90W, 6A	145W, 9.7A	72.5W, 4.8A	225W, 15A	112.5W, 7.5A
GCS250PS18	180W, 10A	90W, 5A	145W, 8.0A	72.5W, 4.0A	250W, 13.9A	125W, 6.9A
GCS250PS24	180W, 7.5A	90W, 3.75A	180W, 7.5A	90W, 3.75A	250W, 10.4A	125W, 5.2A
GCS250PS28	180W, 6.4A	90W, 3.2A	180W, 6.4A	90W, 3.2A	250W, 8.9A	125W, 4.5A
GCS250PS33	180W, 5.5A	90W, 2.7A	180W, 5.5A	90W, 2.7A	250W, 7.6A	125W, 3.8A
GCS250PS36	180W, 5A	90W, 2.5A	180W, 5A	90W, 2.5A	250W, 6.9A	125W, 3.5A
GCS250PS48	180W, 3.75A	90W, 1.88A	180W, 3.75A	90W, 1.88A	250W, 5.2A	125W, 2.6A
GCS250PS56	180W, 3.2A	90W, 1.61A	180W, 3.2A	90W, 1.61A	250W, 4.5A	125W, 2.23A

Model Number	With End Fan		With Top Fan		Forced Air Cooling Without Cover	
	Max Output @50°C	Max Output @70°C	Max Output @50°C	Max Output @70°C	Max Output @50°C	Max Output @70°C
GCS250PS12	225W, 18.7A	112.5W, 9.38A	225W, 18.7A	112.5W, 9.38A	225W, 18.7A	112.5W, 9.38A
GCS250PS15	225W, 15A	112.5W, 7.5A	225W, 15A	112.5W, 7.5A	225W, 15A	112.5W, 7.5A
GCS250PS18	250W, 13.9A	125W, 6.9A	250W, 13.9A	125W, 6.9A	250W, 13.9A	125W, 6.9A
GCS250PS24	250W, 10.4A	125W, 5.2A	250W, 10.4A	125W, 5.2A	250W, 10.4A	125W, 5.2A
GCS250PS28	250W, 8.9A	125W, 4.5A	250W, 8.9A	125W, 4.5A	250W, 8.9A	125W, 4.5A
GCS250PS33	250W, 7.6A	125W, 3.8A	250W, 7.6A	125W, 3.8A	250W, 7.6A	125W, 3.8A
GCS250PS36	250W, 6.9A	125W, 3.5A	250W, 6.9A	125W, 3.5A	250W, 6.9A	125W, 3.5A
GCS250PS48	250W, 5.2A	125W, 2.6A	250W, 5.2A	125W, 2.6A	250W, 5.2A	125W, 2.6A
GCS250PS56	250W, 4.5A	125W, 2.23A	250W, 4.5A	125W, 2.23A	250W, 4.5A	125W, 2.23A

ZERTIFIKAT • CERTIFICATE • CERTIFICADO • CERTIFIKAT • 認證證書

