

# CERTIFICATE OF COMPLIANCE

**Certificate Number** 20181103-E139109  
**Report Reference** E139109-A6044-UL  
**Issue Date** 2018-NOVEMBER-03

**Issued to:** XP POWER L L C  
15641 Red Hill Ave, Suite 100  
Tustin CA 92780

**This certificate confirms that  
representative samples of**

Component - Power Supplies for Use in Audio/Video,  
Information and Communication Technology Equipment  
Switching Power Supply, Models: ECC100US48-XB0201B,  
ECC100USXXYY

Where XX can be any number between 12 and 48, YY can  
be "-F, or "-S", or blank. All "-" considered optional. May  
also be provided with additional suffix "-SF".

Have been investigated by UL in accordance with the  
component requirements in the Standard(s) indicated on  
this Certificate. UL Recognized components are incomplete  
in certain constructional features or restricted in  
performance capabilities and are intended for installation in  
complete equipment submitted for investigation to UL LLC.


**Standard(s) for Safety:** UL 62368-1 and CAN/CSA C22.2 No. 62368-1-14,  
Audio/Video, Information and Communication Technology  
Equipment Part 1: Safety Requirements

**Additional Information:** See the UL Online Certifications Directory at  
<https://iq.ulprospector.com> for additional information.

This *Certificate of Compliance* does not provide authorization to apply the UL Recognized Component Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified  
and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



Bruce Mahrenholz, Director North American Certification Program  
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please  
contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



## UL TEST REPORT AND PROCEDURE

<b>Standard:</b>	UL 62368-1, 2nd Ed, 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1-14, 2nd Ed (Audio/video, information and communication technology equipment Part 1: Safety requirements)
<b>Certification Type:</b>	Component Recognition
<b>CCN:</b>	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
<b>Complementary CCN:</b>	N/A
<b>Product:</b>	Switching Power Supply
<b>Model:</b>	ECC100US48-XB0201B ECC100USXXYY  Where XX can be any number between 12 and 48, YY can be "-F", or "-S", or blank. All "-" considered optional. May also be provided with additional suffix "-SF".
<b>Rating:</b>	Model ECC100US48-XB0201B INPUT ~ 40 - 90VAC 50/60Hz 3A; or 90 Vac square wave OUTPUT 1: 48V DC 1.25A 60W MAX  Model ECC100USXXYY INPUT ~ 100 - 240VAC 50/60Hz 2.5A OUTPUT: See Enclosure - Miscellaneous Ratings Table for details.
<b>Applicant Name and Address:</b>	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By: Adam Tangocci / Project Handler    Reviewed By: Gregory Ray / Reviewer

**Supporting Documentation**

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

A. Authorization - The Authorization page may include additional Factory Identification Code markings.

B. Generic Inspection Instructions -

- i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
- ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
- iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

**Product Description**

The model covered in this report is a component power supply intended for use in Information Technology Equipment. It is an open frame power supply intended for building-in Class I.

**Model Differences**

All models in the Model ECC100USXXYY series, where XX denotes the output voltage, are identical with exception to the Mains Transformer, T1, and minor secondary components that allow for different output voltage ratings. See below for Model Ratings Table Below:

Model ECC100US12: Output Rated: 12 Vdc, 8.1 A; Standby 5.0V, 0.5A

Model ECC100US15: Output Rated: 15 Vdc, 6.5 A; Standby 5.0V, 0.5A

Model ECC100US24: Output Rated: 24 Vdc, 4.1 A; Standby 5.0V, 0.5A

Model ECC100US28: Output Rated: 28 Vdc, 3.5 A; Standby 5.0V, 0.5A

Model ECC100US48: Output Rated: 48 Vdc, 2.0 A; Standby 5.0V, 0.5A

Additional Suffix "F" denotes units provided with additional Input Filter Board.

Additional Suffix "S" denotes units provided with screw terminal.

Additional Suffix "-SF" denotes units provided with Line fuse only.

Model ECC100US48-XB0201B: Input rating 40-90 Vac, 47-63 Hz, Quasi Square Wave; Output rated: 48Vdc, 1.5A.

**Test Item Particulars**

Classification of use by	Ordinary person
Supply Connection	AC Mains ES1
Supply % Tolerance	+10%/-10%
Supply Connection – Type	For building-in
Considered current rating of protective device as part of building or equipment installation	20 A; building;

Equipment mobility	for building-in
Over voltage category (OVC)	OVC II OVC II
Class of equipment	Not Classified
Access location	N/A
Pollution degree (PD)	PD 2
Manufacturer's specified maximum operating ambient	75 °C
IP protection class	IPX0
Power Systems	TN
Altitude during operation (m)	3048 m
Altitude of test laboratory (m)	2000 m or less
Mass of equipment (kg)	0.78

**Technical Considerations**

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer's specification of : 75
- The product is intended for use on the following power systems : TN
- 
- The equipment disconnect device is considered to be : To be determined in the end-product.
- Required Clearances have been adjusted by multiplying the clearance at sea level by a factor of 1.15 for operating at an altitude of 3048 meters. The correction factor is based on barometric pressure of 70kPa. If the calculated Clearance exceeded the Creepage, the Creepage was adjusted to the value of clearance.

**Engineer Conditions of Acceptability**

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Electric Strength
- 
- The following output circuits are at ES1 energy levels : All Outputs
- The following output circuits are at PS3 energy levels : All Outputs
- The maximum investigated branch circuit rating is : 20 A
- 
- The investigated Pollution Degree is : 2
- 
- Proper bonding to the end-product main protective earthing termination is : Required (Class I)
- An investigation of the protective bonding terminals has : Not been conducted
- 
- The following input terminals/connectors must be connected to the end-product supply neutral : AC N
- The following end-product enclosures are required : Mechanical, Fire, Electrical
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C) : L1, L2, L3, T1, and T2 (Class F, 130°C)
- The power supply was evaluated to be used at altitudes up to : "3048 m"
- 
- Heatsinks are floating and considered live. They should not be accessible in the end-product.
- A suitable main disconnect device shall be provided in the end product.
- The power supplies covered by this report have a fuse in the neutral of the primary circuit. The need for a marking to warn a service person of the hazards associated with double pole/neutral fusing shall be considered in the end product.
- Consideration to repeating the Touch Current test should be given in the end-product evaluation.
- The power supplies in this report have been subject to Capacitance Discharge testing. Additional testing should not be needed if directly connected to mains e.g. using an appliance inlet, wiring terminals, etc.

**Additional Information**

Marking Plate is representative of all models.

This report is based on a previous evaluation to IEC 60950-1:2005 (2nd Ed.), Am1:2009 + Am2:20013 under CBTR Ref. No. E139109-A42-CB-3 including Amendments, CBTC Ref. No. CB-US-25908-UL. Based on the previously conducted performance testing, only the tests conducted as part of this investigation were considered necessary.

The following tests were conducted under CTDP SMT/CTF Stage 3 to IEC 60950-1 E2+A1+A2 at XP POWER LLC, 15641 RED HILL AVE, SUITE 100, TUSTIN, CA 92780, USA:

Input: Single-Phase (1.6.2)

Capacitance Discharge (2.1.1.7)

SELV Reliability Test Including Hazardous Voltage Measurements (2.2.2, 2.2.3, 2.2.4, Part 22 6.1)

Humidity (2.9.1, 2.9.2, 5.2.2)

Determination of Working Voltage; Working Voltage Measurement (2.10.2)

Heating (4.5.1, 1.4.12, 1.4.13)

Ball Pressure (4.5.5, 4.5)

Electric Strength (5.2.2)

Component Failure (5.3.1, 5.3.4, 5.3.7)

Abnormal Operation (5.3.1 - 5.3.9)

Transformer Abnormal Operation (5.3.3, 5.3.7b, Annex C.1)

Power Supply Output Short-Circuit/Overload (5.3.7)

The following additional tests were conducted on a sample of model ECC100US15 in accordance with IEC 62368-1:2014 (Second Edition) at XP POWER LLC, 15641 RED HILL AVE, SUITE 100, TUSTIN, CA 92780 USA:

Electric Strength Test (5.4.9)

Prospective Touch Voltage and Touch Current Measurement (5.7)

**Additional Standards**

The product fulfills the requirements of: EN 62368-1:2014 + A11:2017

**Markings and Instructions**

Clause Title	Marking or Instruction Details
Equipment identification marking – Manufacturer identification	Listees or Recognized companys name, Trade Name, Trademark or File Number
Equipment identification marking – model identification	Model Number
Equipment rating marking – ratings	"Input Ratings (voltage, frequency/dc, current/power)", "Output Ratings (voltage, frequency/dc, current/power)"
Warning to service personnel	"CAUTION: Double pole, neutral fusing. Disconnect mains before servicing. "/"ATTENTION. Double pôle/fusible sur le neutre. Débrancher l'alimentation avant l'entretien."

**Special Instructions to UL Representative**

--