



Product Service

CERTIFICATE

No. B 057396 0437 Rev. 01

Output Power under different configurations:

Model Number	Convectional Cooling Without Cover		Convectional Cooling With Cover		Forced Air Cooling With Cover	
	Max Output @50°C	Max Output @70°C	Max Output @50°C	Max Output @70°C	Max Output @50°C	Max Output @70°C
GCS265PS12	V1:180W, 15A V2: 10W, 2A	V1: 90W, 7.5A V2: 5W, 1A	V1: 140W, 11.67A V2: 10W, 2A	V1: 70W, 5.83A V2: 5W, 1A	V1: 250W, 20.8 V2: 15W, 3A	V1: 125W, 10.4A V2: 7.5W, 1.5A
GCS265PS15	V1:180W, 12A V2: 10W, 2A	V1: 90W, 6A V2: 5W, 1A	V1: 140W, 9.33A V2: 10W, 2A	V1: 70W, 4.67A V2: 5W, 1A	V1: 250W, 16.7A V2: 15W, 3A	V1: 125W, 8.3A V2: 7.5W, 1.5A
GCS265PS18	V1:180W, 10A V2: 10W, 2A	V1: 90W, 5A V2: 5W, 1A	V1: 140W, 7.78A V2: 10W, 2A	V1: 70W, 3.89A V2: 5W, 1A	V1: 250W, 13.9A V2: 15W, 3A	V1: 125W, 6.9A V2: 7.5W, 1.5A
GCS265PS24	V1: 180W, 7.5A V2: 10W, 2A	V1: 90W, 3.75A V2: 5W, 1A	V1: 140W, 5.83A V2: 10W, 2A	V1: 70W, 2.92A, V2: 5W, 1A	V1: 250W, 10.4A V2: 15W, 3A	V1: 125W, 5.2A V2: 7.5W, 1.5A
GCS265PS28	V1: 180W, 6.4A V2: 10W, 2A	V1: 90W, 3.21A V2: 5W, 1A	V1: 140W, 5A V2: 10W, 2A	V1: 70W, 2.5A, V2: 5W, 1A	V1: 250W, 8.9A V2: 15W, 3A	V1: 125W, 4.5A V2: 7.5W, 1.5A
GCS265PS33	V1: 180W, 5.5A V2: 10W, 2A	V1: 90W, 2.72A V2: 5W, 1A	V1: 140W, 4.24A V2: 10W, 2A	V1: 70W, 2.12A, V2: 5W, 1A	V1: 250W, 7.6A V2: 15W, 3A	V1: 125W, 3.8A V2: 7.5W, 1.5A
GCS265PS36	V1: 180W, 5A V2: 10W, 2A	V1: 90W, 2.5A V2: 5W, 1A	V1: 140W, 3.89A V2: 10W, 2A	V1: 70W, 1.94A, V2: 5W, 1A	V1: 250W, 6.9A V2: 15W, 3A	V1: 125W, 3.5A V2: 7.5W, 1.5A
GCS265PS48	V1: 180W, 3.75A V2: 10W, 2A	V1: 90W, 1.875A V2: 5W, 1A	V1: 140W, 2.92A V2: 10W, 2A	V1: 70W, 1.46A V2: 5W, 1A	V1: 250W, 5.2A V2: 15, 3A	V1: 125W, 2.6A V2: 7.5W, 1.5A
GCS265PS56	V1: 180W, 3.2A V2: 10W, 2A	V1: 90W, 1.61A V2: 5W, 1A	V1: 140W, 2.5A V2: 10W, 2A	V1: 70W, 1.25A V2: 5W, 1A	V1: 252W, 4.5A V2: 15W, 3A	V1: 125W, 2.23A V2: 7.5W, 1.5A

Model Number	With End Fan		With Top Fan		Forced Air Cooling Without Cover	
	Max Output @50°C	Max Output @70°C	Max Output @50°C	Max Output @70°C	Max Output @50°C	Max Output @70°C
GCS265PS12	V1: 250W, 20.8A V2: 15W, 3A	V1: 125W, 10.4A V2: 7.5W, 1.5A	V1: 250W, 20.8A V2: 15W, 3A	V1: 125W, 10.4A V2: 7.5W, 1.5A	V1: 250W, 20.8A V2: 15W, 3A	V1: 125W, 10.4A V2: 7.5W, 1.5A
GCS265PS15	V1: 250W, 16.7A V2: 15W, 3A	V1: 125W, 8.3A V2: 7.5W, 1.5A	V1: 250W, 16.7A V2: 15W, 3A	V1: 125W, 8.3A V2: 7.5W, 1.5A	V1: 250W, 16.7A V2: 15W, 3A	V1: 125W, 8.3A V2: 7.5W, 1.5A
GCS265PS18	V1: 250W, 13.9A V2: 15W, 3A	V1: 125W, 6.9A V2: 7.5W, 1.5A	V1: 250W, 13.9A V2: 15W, 3A	V1: 125W, 6.9A V2: 7.5W, 1.5A	V1: 250W, 13.9A V2: 15W, 3A	V1: 125W, 6.9A V2: 7.5W, 1.5A
GCS265PS24	V1: 250W, 10.4A V2: 15W, 3A	V1: 125W, 5.2A, V2: 7.5W, 1.5A	V1: 250W, 10.4A V2: 15W, 3A	V1: 125W, 5.2A V2: 7.5W, 1.5A	V1: 250W, 10.4A V2: 15W, 3A	V1: 125W, 5.2A V2: 7.5W, 1.5A
GCS265PS28	V1: 250W, 8.9A V2: 15W, 3A	V1: 125W, 4.5A, V2: 7.5W, 1.5A	V1: 250W, 8.9A V2: 15W, 3A	V1: 125W, 4.5A V2: 7.5W, 1.5A	V1: 250W, 8.9A V2: 15W, 3A	V1: 125W, 4.5A V2: 7.5W, 1.5A
GCS265PS33	V1: 250W, 7.6A V2: 15W, 3A	V1: 125W, 3.8A, V2: 7.5W, 1.5A	V1: 250W, 7.6A V2: 15W, 3A	V1: 125W, 3.8A V2: 7.5W, 1.5A	V1: 250W, 7.6A V2: 15W, 3A	V1: 125W, 3.8A V2: 7.5W, 1.5A
GCS265PS36	V1: 250W, 6.9A V2: 15W, 3A	V1: 125W, 3.5A, V2: 7.5W, 1.5A	V1: 250W, 6.9A V2: 15W, 3A	V1: 125W, 3.5A V2: 7.5W, 1.5A	V1: 250W, 6.9A V2: 15W, 3A	V1: 125W, 3.5A V2: 7.5W, 1.5A
GCS265PS48	V1: 250W, 5.2A V2: 15W, 3A	V1: 125W, 2.6A V2: 7.5W, 1.5A	V1: 250W, 5.2A V2: 15W, 3A	V1: 125W, 2.6A V2: 7.5W, 1.5A	V1: 250W, 5.2A V2: 15W, 3A	V1: 125W, 2.6A V2: 7.5W, 1.5A
GCS265PS56	V1: 252W, 4.5A V2: 15W, 3A	V1: 125W, 2.23A V2: 7.5W, 1.5A	V1: 252W, 4.5A V2: 15W, 3A	V1: 125W, 2.25A V2: 7.5W, 1.5A	V1: 252W, 4.5A V2: 15W, 3A	V1: 125W, 2.23A V2: 7.5W, 1.5A

V2: 5V Standby Output

TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD
 ZERTIFIKAT ◆ CERTIFICATE ◆ 認證證書 ◆ СЕРТИФИКАТ ◆ CERTIFICADO ◆ CERTIFICAT

