

CERTIFICATE OF COMPLIANCE

Certificate Number 20170821-E139109
Report Reference E139109-A173-UL
Issue Date 2017-AUGUST-21

Issued to: XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780


**This is to certify that
representative samples of**

COMPONENT - POWER SUPPLIES, INFORMATION TECHNOLOGY
EQUIPMENT INCLUDING ELECTRICAL BUSINESS EQUIPMENT ,
COMPONENT - POWER SUPPLIES FOR USE WITH AUDIO/VIDEO,
INFORMATION AND COMMUNICATION TECHNOLOGY EQUIPMENT
See Addendum page for models

Have been investigated by UL in accordance with the
Standard(s) indicated on this Certificate.

Standard(s) for Safety: See Addendum page for Standard(s) for Safety
Additional Information: See the UL Online Certifications Directory at
www.ul.com/database for additional information

Only those products bearing the UL Certification Mark should be considered as being covered by UL's
Certification and Follow-Up Service.

The UL Recognized Component Mark generally consists of the manufacturer's identification and catalog
number, model number or other product designation as specified under "Marking" for the particular
Recognition as published in the appropriate UL Directory. As a supplementary means of identifying products
that have been produced under UL's Component Recognition Program, UL's Recognized Component Mark:
, may be used in conjunction with the required Recognized Marks. The Recognized Component Mark is
required when specified in the UL Directory preceding the recognitions or under "Markings" for the individual
recognitions.

Recognized components are incomplete in certain constructional features or restricted in performance
capabilities and are intended for use as components of complete equipment submitted for investigation rather
than for direct separate installation in the field. The final acceptance of the component is dependent upon its
installation and use in complete equipment submitted to UL LLC.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Director North American Certification Program
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please
contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>.



CERTIFICATE OF COMPLIANCE

Certificate Number 20170821-E139109
Report Reference E139109-A173-UL
Issue Date 2017-AUGUST-21

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Product/Models;

Power supply for building-in, switch mode type – model:

ECF40USXX Series, where XX can be any number between 12 and 48 designating the output voltage, may also be followed by suffix SF.

Standard(s) for Safety:

UL 60950-1 and CAN/CSA C22.2 No. 60950-1-07 - Information Technology Equipment - Safety - Part 1: General Requirements



Bruce Mahrenholz, Director North American Certification Program
UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>.



UL TEST REPORT AND PROCEDURE

Standard:	UL 60950-1, 2nd Edition, 2014-10-14 (Information Technology Equipment - Safety - Part 1: General Requirements) CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10 (Information Technology Equipment - Safety - Part 1: General Requirements)
Certification Type:	Component Recognition
CCN:	QQGQ2, QQGQ8 (Power Supplies for Information Technology Equipment Including Electrical Business Equipment)
Complementary CCN:	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
Product:	Power supply for building-in, switch mode type
Model:	ECF40USXX Series, where XX can be any number between 12 and 48 designating the output voltage, may also be followed by suffix SF.
Rating:	Input: 100-240 Vac, 50/60Hz, 1.2A Max. Output: See Model Differences for details.
Applicant Name and Address:	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared by: Robert Leon/Project Handler

Reviewed by: Walid Beytoughan/Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The models covered in this Test Report are component AC-DC power supplies intended for use in Information Technology Equipment. The switching power supplies are open frame type intended for building-in.

Model Differences

All models in the ECF40USXX series are identical with exception to model designation, Transformer (T1) and secondary components/circuitry that allow for different output voltage ratings.

Model output ratings as follows.

- Model ECF40US12: Output Rated: 10.1 Vdc - 13.5 Vdc, 3.34 A Max., 40 W Max.
- Model ECF40US15: Output Rated: 13.6 Vdc - 17 Vdc, 2.67 A Max., 40 W Max.
- Model ECF40US18: Output Rated: 17.1 Vdc - 21 Vdc, 2.23 A Max., 40 W Max.
- Model ECF40US24: Output Rated: 21.1 Vdc - 26 Vdc, 1.67 A Max., 40 W Max.
- Model ECF40US28: Output Rated: 26.1 Vdc - 31 Vdc, 1.43 A Max., 40 W Max.
- Model ECF40US36: Output Rated: 33.1 Vdc - 42 Vdc, 1.11 A Max., 40 W Max.
- Model ECF40US48: Output Rated: 42.1 Vdc - 54 Vdc, 0.83 A Max., 40 W Max.

Technical Considerations

- Equipment mobility : for building-in
- Connection to the mains : for building-in
- Operating condition : continuous
- Access location : for building-in
- Over voltage category (OVC) : OVC II
- Mains supply tolerance (%) or absolute mains supply values : +10% / -10%
- Tested for IT power systems : Yes
- IT testing, phase-phase voltage (V) : 230
- Class of equipment : To be determined by end-product
- Considered current rating of protective device as part of the building installation (A) : 20 A
- Pollution degree (PD) : PD 2
- IP protection class : IP X0
- Altitude of operation (m) : 5000 m

- Altitude of test laboratory (m) : 17 m
- Mass of equipment (kg) : 0.07 kg
- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: 50°C at full rated load. 70°C at 50% rated load.
- The means of connection to the mains supply is: For building-in. To be evaluated in end-product.
- The product is intended for use on the following power systems: TN / IT
- The equipment disconnect device is considered to be: For building-in. To be evaluated in end-product.
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this Test Report)
- The following accessible locations (with circuit/schematic designation) are within a limited current circuit: Load Side of Bridging Capacitor (CY1).

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following Production-Line tests are conducted for this product: Electric Strength
- The end-product Electric Strength Test is to be based upon a maximum working voltage of: Primary-SELV: 240 Vrms / 340 Vpk, Primary-Earthed Dead Metal: 240 Vrms / 340 Vpk
- The following secondary output circuits are at hazardous energy levels: All outputs
- The power supply terminals and/or connectors are: Suitable for factory wiring only
- The maximum investigated branch circuit rating is: 20 A
- The investigated Pollution Degree is: 2
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C): TR1 (Class F / 155°C)
- The following end-product enclosures are required: Electrical / Fire / Mechanical
- Suitable disconnect device is to be provided in the end-product.
- In accordance with IEC60664-1, Table A2, required clearances were adjusted by multiplying the clearance at sea level by a factor of 1.48 for operating at an altitude of 5000 m. The correction factor is based on barometric pressure of 70 kPa and Overvoltage Category II. If the calculated clearance exceeded the creepage, the creepage was adjusted to the value of clearance. No other additional requirements were considered at this time and are not explicitly addressed in UL 60950-1.
- Printed Wiring Board rated 130°C.
- The power supply is provided with a fuse in both the line and neutral of the primary circuit. The need for a marking warning service person of the hazards associated with neutral fusing shall be considered in the end-product.
- Heating (Thermal Requirements) Test was not conducted on power supply with input/output leads. If power supply is provided with input and/or output leads, then temperature on leads must be measured and cannot exceed 105°C.

Additional Information

The switching power supply series covered by this Test Report used Double/Reinforced Insulation between Primary and Secondary circuits.

Licenses older than 3 years to be provided by the manufacturer upon request.

Additional Standards	
The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013, IEC 60950-1:2005 + A1:2009 + A2:2013, UL 62368-1 2nd Ed., CSA C22.2 No. 62368-1-14	
Markings and instructions	
Clause Title	Marking or Instruction Details
Power rating - Ratings	Ratings (voltage, frequency/dc, current)
Power rating - Company identification	Listee's or Recognized company's name, Trade Name, Trademark or File Number
Power rating - Model	Model Number
Fuses - Non-operator access/soldered-in fuses	Unambiguous reference to service documentation for instructions for replacement of fuses replaceable only by service personnel
Special Instructions to UL Representative	
N/A	

Production-Line Testing Requirements						
<u>Electric Strength Test Special Constructions - Refer to Generic Inspection Instructions, Part AC for further information.</u>						
Model	Component	Removable Parts	Test probe location	V rms	V dc	Test Time, s
ECF40USXX	TR1	-	Primary/Secondary	300 0	4200	1
<u>Earthing Continuity Test Exemptions - This test is not required for the following models:</u>						
All						
<u>Electric Strength Test Exemptions - This test is not required for the following models:</u>						
N/A						
<u>Electric Strength Test Component Exemptions - The following solid-state components may be disconnected from the remainder of the circuitry during the performance of this test:</u>						
N/A						
<u>Sample and Test Specifics for Follow-Up Tests at UL</u>						
Model	Component	Material	Test	Sample(s)	Test Specifics	
N/A						