Ref. Certif. No.

DK-181342-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	DC to DC Converter
Name and address of the applicant	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the manufacturer	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the factory Note: *When more than one factory, please report on page 2*	No. 8-1 Fu Kung Rd., Fu Hsing Park Fu Hsing Hsiang, Chang Hua Hsien, 506 Taiwan ☒ Additional Information on page 2
Ratings and principal characteristics	(Optional) Input:9-40V⎓, 67A for HBT500T24SYY-ZZZ, 6.5-75⎓, 34A for HBT500T48SYY-ZZZ, 16-40⎓, 45A for HBT650C24SYY-ZZZ, Output: See test report for details
Trademark / Brand (if any)	XP Power
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	HBT500TXXSYY-ZZZ, HBT650C24SYY-ZZZ ☒ Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	Evaluated to National or Group Differences for AR, AU, CA, CN, EU Group Differences, JP, NZ, KR, SA, GB, US ☒ Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2018
As shown in the Test Report Ref. No. which forms part of this Certificate	2604062-CB issued on 2026-06-01

This CB Test Certificate is issued by the National Certification Body

UL Solutions

☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-06-03

Signature:

Thomas Wilson

Ref. Certif. No.

DK-181342-UL

Factory(ies):

No.66 Yuanying Rd., Liaobu Town, Dongguan City, Guangdong 523412,
P.R. China

Additional Model Detail(s):

HBT500TXXSYY-ZZZ, HBT650C24SYY-ZZZ, “XX” can be 24 or 48
“YY” can be 12, 24, 28, 48 or 54
“ZZZ” can be blank, “-” or any alphanumeric characteristic

Evaluated to National Differences declared for:

EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020

Additional information (if necessary)

☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-06-03

Signature:

Thomas Wilson