



Product Service

CERTIFICATE

No. B 057396 0387 Rev. 01

Output Module Name	Rating	Output Module Name	Rating
SZ	1.8V @ 50A	U3	5.0V @ 40A; 15.0V @ 4.0A
S1	2.5V @ 50A	U4	5.0V @ 40A; 24.0V @ 2.5A
S2	3.3V @ 50A		
S3	5.0V @ 50A	R6	5.0V @ 8A; 12.0V @ 6.0A
SF	8.0V @ 31A	R4	5.0V @ 8A; 24.0V @ 3.0A
SG	10.0V @ 25A	R1	12.0V @ 6A; 12.0V @ 6.0A
S4	12.0V @ 20A	R5	12.0V @ 6A; 24.0V @ 3.0A
S5	15.0V @ 17A	R2	15.0V @ 5A; 15.0V @ 5.0A
S6	24.0V @ 10A		
S7	28.0V @ 9A	T3	3.3V @ 20A; 12.0V @ 4.0A; 12.0V@4A
S8	36.0V @ 7A	T4	3.3V @ 20A; 15.0V @ 3.0A; 15.0V @ 3A
S9	48.0V @ 5A	T1	5.0V @ 20A; 12.0V @ 4.0A; 12.0V @ 4A
		T2	5.0V @ 20A; 15.0V @ 3.0A; 15.0V @ 3A
U5	3.3V @ 40A; 5.0V @ 4.0A	T8	5.0V @ 20A; 12.0V @ 4.0A; 5.0V @ 4A
U6	3.3V @ 40A; 12.0V @ 4.0A	T6	12.0V @ 10A; 12.0V @ 4.0A; 5.0V @ 4A
U7	3.3V @ 40A; 15.0V @ 4.0A	T10	12.0V @ 10A; 12.0V @ 4.0A; 15.0V @ 3A
U8	3.3V @ 40A; 24.0V @ 2.5A	T11	24.0V @ 4A; 5.0V @ 4.0A; 5.0V @ 4A
U1	5.0V @ 40A; 5.0V @ 4.0A	T9	24.0V @ 4A; 15.0V @ 4.0A; 5.0V @ 4A
U2	5.0V @ 40A; 12.0V @ 4.0A	T7	24.0V @ 4A; 15.0V @ 3.0A; 5.0V @ 3A

Fan Assembly style:

Blank for U-Channel or combinations of letter E, F or T and any number 0-9 for different fan styles.

Parallel Option:

Blank if not required or 00-99 for different parallel options.

Note: "-" can be optionally used between different sections of model number.

TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD
ZERTIFIKAT ◆ CERTIFICATE ◆ 認 證 證 書 ◆ CERTIFICADO ◆ CERTIFICAT



Product Service

CERTIFICATE

No. B 057396 0387 Rev. 01

Conditions of Acceptability:

When installing the equipment, all requirements of the standards and the manufacturer's specifications must be met.

The models require:

- A suitable electrical and fire enclosure must be provided in the end use equipment.
- The product is intended for use on the following power systems: TN.
- The following output circuits are at ES1 energy levels: All.
- The following output circuits are at PS3 energy levels: All.
- Sufficient clearance and creepage distance shall be provided between the primary circuit and accessible conductive parts.
- The following input terminals/connectors must be connected to the end-product supply neutral: AC N.
- Heatsinks are floating and considered live. They shall not be accessible in the end product.
- A suitable main disconnect device shall be provided in the end product.
- Proper bonding to the end-product main protective earthing terminal is required when installed in Class I end product, ground bond test shall be conducted.
- Touch current test and dielectric Strength test need to be considered at end use equipment.
- The power supplies have a fuse in the neutral of the primary circuit. A warning for service persons to be considered in the end product.

Tested according to: EN 62368-1:2014/A11:2017

Production Facility(ies): 059061, 071712, 089850, 059319

TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD TÜV SÜD
ZERTIFIKAT ◆ CERTIFICATE ◆ 認證證書 ◆ CERTIFICADO ◆ CERTIFICAT