



CERTIFICATE

No. B 057396 1158 Rev. 00

Holder of Certificate: **XP Power LLC.**
340 Commerce, Suite 100
Irvine CA 92602
USA

Certification Mark:




Product: **Power supply
(Power Supply)**

The product was tested on a voluntary basis and complies with the essential requirements.
The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier.
All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6121026013901

Valid until: 2031-05-25

Date, 2026-06-12


(Watson Yang)



CERTIFICATE

No. B 057396 1158 Rev. 00

Model(s): UCH750PSxxC2zz
 ('xx' can be 12, 24, 36, 48, 54 or 56 for output voltage; 'zz' can be -C (with top cover) or blank (open frame type))

Brand Name: XP Power


Parameters:

Rated inputs:	100-240 V~, 50-60 Hz, 9.3-3.2 A
Rated outputs:	See below
Protection class:	Class II
Max. ambient temperature:	50 °C
Protection class:	IPX0

Remark:
 The equipment is evaluated for operating in altitude up to 5,000 m above the sea level.

CERTIFICATE

No. B 057396 1158 Rev. 00

The output rating of models are as below:

Model No	Output Rated
UCH750PS12C2	12.0 V  62.5 A 5.0 V  2.0 A Total Power 760.0 W Max.
UCH750PS24C2	24.0 V  31.25 A 5.0 V  2.0 A Total Power 760.0 W Max.
UCH750PS36C2	36.0 V  20.83 A 5.0 V  2.0 A Total Power 759.88 W Max.
UCH750PS48C2	48.0 V  15.62 A 5.0 V  2.0 A Total Power 759.76 W Max.
UCH750PS54C2	54.0 V  13.88 A 5.0 V  2.0 A Total Power 759.52 W Max.
UCH750PS56C2	56.0 V  13.4 A 5.0 V  2.0 A Total Power 760.4 W Max.
UCH750PS12C2-C	12.0 V  62.5 A 5.0 V  2.0 A Total Power 760.0 W Max.
UCH750PS24C2-C	24.0 V  31.25 A 5.0 V  2.0 A Total Power 760.0 W Max.
UCH750PS36C2-C	36.0 V  20.83 A 5.0 V  2.0 A Total Power 759.88 W Max.
UCH750PS48C2-C	48.0 V  15.62 A 5.0 V  2.0 A Total Power 759.76 W Max.
UCH750PS54C2-C	54.0 V  13.88 A 5.0 V  2.0 A Total Power 759.52 W Max.
UCH750PS56C2-C	56.0 V  13.4 A 5.0 V  2.0 A Total Power 760.4 W Max.

Tested according to: EN IEC 62368-1:2024/A11:2024