



CERTIFICATE

No. B 057396 1157 Rev. 00

Holder of Certificate: **XP Power LLC.**
340 Commerce, Suite 100
Irvine CA 92602
USA

Certification Mark:




Product: **Power supply
(Power Supply)**

The product was tested on a voluntary basis and complies with the essential requirements.
The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier.
All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 6121026013801

Valid until: 2031-05-25

Date, 2026-06-12


(Watson Yang)



CERTIFICATE

No. B 057396 1157 Rev. 00

Model(s): UCH750PSxxzz
 ('xx' can be 12, 24, 36, 48, 54 or 56 for output voltage; 'zz' can be –C (with top cover) or blank (open frame type))

Brand Name: XP Power


Parameters:

Rated inputs:	100-240 V~, 50-60 Hz, 9.3-3.2 A
Rated outputs:	See below
Protection class:	Class I
Max. ambient temperature:	50 °C

Remark:
 The equipment is evaluated for operating in altitude up to 5,000 m above the sea level.

CERTIFICATE

No. B 057396 1157 Rev. 00

The output rating of models are as below:

Model No	Output Rated
UCH750PS12	12.0 V  62.5 A 5.0 V  2.0 A Total Power 760.0 W Max.
UCH750PS24	24.0 V  31.25 A 5.0 V  2.0 A Total Power 760.0 W Max.
UCH750PS36	36.0 V  20.83 A 5.0 V  2.0 A Total Power 759.88 W Max.
UCH750PS48	48.0 V  15.62 A 5.0 V  2.0 A Total Power 759.76 W Max.
UCH750PS54	54.0 V  13.88 A 5.0 V  2.0 A Total Power 759.52 W Max.
UCH750PS56	56.0 V  13.4 A 5.0 V  2.0 A Total Power 760.4 W Max.
UCH750PS12-C	12.0 V  62.5 A 5.0 V  2.0 A Total Power 760.0 W Max.
UCH750PS24-C	24.0 V  31.25 A 5.0 V  2.0 A Total Power 760.0 W Max.
UCH750PS36-C	36.0 V  20.83 A 5.0 V  2.0 A Total Power 759.88 W Max.
UCH750PS48-C	48.0 V  15.62 A 5.0 V  2.0 A Total Power 759.76 W Max.
UCH750PS54-C	54.0 V  13.88 A 5.0 V  2.0 A Total Power 759.52 W Max.
UCH750PS56-C	56.0 V  13.4 A 5.0 V  2.0 A Total Power 760.4 W Max.

Tested according to: EN IEC 62368-1:2024/A11:2024