



Product Service

# CERTIFICATE

No. B 12 03 65969 078

**Holder of Certificate: XP Power Limited**401 Commonwealth Drive,  
Haw Par Technocentre, Lobby B, #02-02 149598  
SINGAPORE**Certification Mark:****Product:****Switch mode power supplies  
(Switching Mode Power Supply)**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

**Test report no.:**

68230813704A

( Alex Kong )

**Date,** 2012-03-19

Page 1 of 3





Product Service

**CERTIFICATE**

No. B 12 03 65969 078

**Model(s):** **VCP05US series**  
(see page 3 for details of model number)

**Parameters:**

|                        |                            |
|------------------------|----------------------------|
| Rated Input :          | 100-240VAC, 50/60Hz, 200mA |
| Rated Output :         | See page 3 for details     |
| Construction :         | Built-in                   |
| Protection Class :     | Consider in end system     |
| Degree of Protection : | IPX0                       |

Remarks:

- Built-in type equipment, suitable enclosure should be provided by end system.
- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Maximum operating temperature is 50°C.

**Tested according to:** EN 60950-1/A12:2011

**Production Facility(ies):** 49020

**CERTIFICATE**  
**No: B 12 03 65969 078**



Product Service

| Model No   | Output Voltage (V) | Max Load Current (A) | Max Output Power(W) |
|------------|--------------------|----------------------|---------------------|
| VCP05US03  | 3.00               | 0.01-1.20            | 3.6                 |
| VCP05US033 | 3.30               | 0.01-1.20            | 3.96                |
| VCP05US035 | 3.50               | 0.01-1.20            | 4.2                 |
| VCP05US04  | 4.00               | 0.01-1.20            | 4.8                 |
| VCP05US045 | 4.50               | 0.01-1.00            | 4.5                 |
| VCP05US05  | 5.00               | 0.01-1.00            | 5.0                 |
| VCP05US052 | 5.20               | 0.01-1.00            | 5.2                 |
| VCP05US06  | 6.00               | 0.01-0.80            | 4.8                 |
| VCP05US066 | 6.60               | 0.01-0.80            | 5.28                |
| VCP05US07  | 7.00               | 0.01-0.65            | 4.55                |
| VCP05US075 | 7.50               | 0.01-0.60            | 4.5                 |
| VCP05US08  | 8.00               | 0.01-0.60            | 4.8                 |
| VCP05US09  | 9.00               | 0.01-0.55            | 4.95                |
| VCP05US10  | 10.0               | 0.01-0.50            | 5.0                 |
| VCP05US12  | 12.0               | 0.01-0.40            | 4.8                 |
| VCP05US138 | 13.8               | 0.01-0.35            | 4.83                |
| VCP05US15  | 15.0               | 0.01-0.30            | 4.5                 |