





Product Service

CERTIFICATE

No. B 057396 0563 Rev. 00

Model(s):

VCT40USX, VCT60USY

Where X is 05, 053, Y is 12, 15, 16, 18, 19, 20, 24, 30

Brand Name:

XP



Parameters:

Rated Input: 100-240 Vac
Rated Input Current: 1.0A: VCT40USX
1.7A: VCT60USY
Rated Input Frequency: 50-60 Hz, 400Hz
DC Output Ratings: See below for output ratings
Elevation for use: 0-3048 m above sea level
Protection Class: Class I
Maximum temperature,
ambient: 50°C

General Product information:

The model covered in this report is a component power supply intended for use in Audio/video, information and communication technology equipment. It is an open frame power supply intended for building-in Class I end-products.



Product Service

CERTIFICATE

No. B 057396 0563 Rev. 00

Rated Outputs for Models:

Model VCT40US05
INPUT ~ 100-240VAC, 1.0A 50-60Hz, 400Hz
OUTPUT: 5V dc 8A 40W max

Model VCT40US053
INPUT ~ 100-240VAC, 1.0A 50-60Hz, 400Hz
OUTPUT: 5.3V dc 7.55A 40W max

Model VCT60US12
INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz
OUTPUT: 12V dc 5.00A

Model VCT60US15
INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz
OUTPUT: 15V dc 4.00A

Model VCT60US16
INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz
OUTPUT: 16V dc 3.75A

Model VCT60US18
INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz
OUTPUT: 18V dc 3.33A

Model VCT60US19
INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz
OUTPUT: 19V dc 3.16A

Model VCT60US20
INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz
OUTPUT: 20V dc 3.00A

Model VCT60US24
INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz
OUTPUT: 24V dc 2.50A

Model VCT60US30
INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz
OUTPUT: 30V dc 2.00A



Product Service

CERTIFICATE

No. B 057396 0563 Rev. 00

Conditions of Acceptability:

When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Electric Strength
- The following output circuits are at ES1 energy levels : All Outputs
- The following output circuits are at PS3 energy levels : All Outputs
- The maximum investigated branch circuit rating is : 20 A
- The investigated Pollution Degree is : 2
- Proper bonding to the end-product main protective earthing termination is : Required (Class I)
- An investigation of the protective bonding terminals has : Not been conducted
- The following input terminals/connectors must be connected to the end-product supply neutral : AC N
- The following end-product enclosures are required : Mechanical, Fire, Electrical
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C) : T1 - Class 130(B)
- The power supply was evaluated to be used at altitudes up to : "3048 m"
- When installed in a Class I end product, the power supply shall be mounted in a manner that provides the minimum required Clearance between the primary side of power supply and protectively earthed accessible conductive parts.
- Heatsinks are floating and considered live. They should not be accessible in the end-product.
- A suitable main disconnect device shall be provided in the end product.
- Consideration to repeating the Touch Current test should be given in the end-product evaluation.
- The power supplies in this report have been subject to Capacitance Discharge testing. Additionally, all associated component safeguards have been assessed to the applicable requirement in Annex G.10. Additional testing should not be needed if directly connected to mains e.g. using an appliance inlet, wiring terminals, etc
- When installed in a Class II end product, the power supply shall be mounted on insulating posts in a manner that provides the minimum required Clearance between the power supply and any accessible conductive parts

Tested according to: EN 62368-1:2014/A11:2017

**Production
Facility(ies):** 083459