



QQHM2.E321744 Power Supplies, Medical and Dental - Component

Page Bottom

Power Supplies, Medical and Dental - Component

See General Information for Power Supplies, Medical and Dental - Component

XP POWER L L C

E321744

SUITE 150

1241 E DYER RD

SANTA ANA, CA 92705 USA

Model No.	Rated Input			Max Output				OC	SP	EP	FC	GC
	Volts	Hz	SC	V	A	VA						
"Switching Power Supply".												
AFM120PS12[*r]												
	100-240ac	50-60	0	12.0dc	0.01-8.33	-	9	60601-1	20B	0	2	
AFM120PS12C6[*r]												
	100-240ac	50-60	0	12.0dc	0.01-8.33	-	9	60601-1	20B	0	2	
AFM120PS135[*r]												
	100-240ac	50-60	0	13.5dc	0.01-7.40	-	9	60601-1	20B	0	2	
AFM120PS135C6[*r]												
	100-240ac	50-60	0	13.5dc	0.01-7.40	-	9	60601-1	20B	0	2	
AFM120PS138[*r]												
	100-240ac	50-60	0	13.8dc	0.01-7.25	-	9	60601-1	20B	0	2	
AFM120PS138C6[*r]												
	100-240ac	50-60	0	13.8dc	0.01-7.25	-	9	60601-1	20B	0	2	
AFM120PS15[*r]												
	100-240ac	50-60	0	15.0dc	0.01-6.66	-	9	60601-1	20B	0	2	
AFM120PS15C6[*r]												
	100-240ac	50-60	0	15.0dc	0.01-6.66	-	9	60601-1	20B	0	2	
AFM120PS16[*r]												
	100-240ac	50-60	0	16.0dc	0.01-6.25	-	9	60601-1	20B	0	2	
AFM120PS16C6[*r]												
	100-240ac	50-60	0	16.0dc	0.01-6.25	-	9	60601-1	20B	0	2	
AFM120PS17[*r]												
	100-240ac	50-60	0	17.0dc	0.01-5.88	-	9	60601-1	20B	0	2	
AFM120PS17C6[*r]												
	100-240ac	50-60	0	17.0dc	0.01-5.88	-	9	60601-1	20B	0	2	
AFM120PS18[*r]												
	100-240ac	50-60	0	18.0dc	0.01-5.55	-	9	60601-1	20B	0	2	
AFM120PS18C6[*r]												

	100-240ac	50-60	0	5	5.0	45	9	2601-1	20B	0	0
				24	2.0	-	9				
PMP55-31 (c)											
	100-240ac	50-60	0	5	5.0	45	9	2601-1	20B	0	0
				12	3.0	-	9				
				-12	0.5	-	9				
PMP55-31-3D (c)											
	100-240ac	50-60	0	5	4.0	45	9	2601-1	20B	0	0
				12	1.0	-	9				
				-12	1.0	-	9				
PMP55-32 (c)											
	100-240ac	50-60	0	5	5.0	45	9	2601-1	20B	0	0
				15	2.5	-	9				
				-15	0.5	-	9				
SDM300PD0512yy-z(h)											
	100-240ac	47-63	0	5dc	24	-	9	ES60601-1	20B	0	1
				12dc	13.33	-	9				
				-	-	Total 240	-				
SDM300PD1224yy-z(h)											
	100-240ac	47-63	0	12dc	13.33	-	9	ES60601-1	20B	0	1
				24dc	6.67	-	9				
				-	-	total 240	9				
SDM300PS12yy-z(h)											
	100-240ac	47-63	0	13.8dc	25	300	9	ES60601-1	20B	0	1
SDM300PS15yy-z(h)											
	100-240ac	47-63	0	16dc	21.43	300	9	ES60601-1	20B	0	1
SDM300PS24yy-z(h)											
	100-240ac	47-63	0	28dc	13.04	300	9	ES60601-1	20B	0	1
SDM300PS36yy-z(h)											
	100-240ac	47-63	0	43dc	8.57	300	9	ES60601-1	20B	0	1
SDM300PS48yy-z(h)											
	100-240ac	47-63	0	52dc	6.82	300	9	ES60601-1	20B	0	1
SDS150PS12B-M, SDS150PS12-M, SDS150PS12B-MD, SDS150PS12-MD											
	100-240ac	47-63	0	12.2	14	157.76	9	60601-1	20B	0	2
SDS150PS24B-M, SDS150PS24-M, SDS150PS24B-MD, SDS150PS24-MD											
	100-240ac	47-63	0	24.17	7.6	176.47	9	60601-1	20B	0	2
SDU150PS12-D,SDU150PS12B-D,SDU150PS12,SDU150PS12B[*r]											
	100-240ac	47-63	0	-	12.5	150 W	0	ANSI/AAMI ES 60601-1: 2005	20B	0	1
SDU150PS24-D,SDU150PS24B-D,SDU150PS24,SDU150PS24B[*r]											
	100-240ac	47-63	0	-	6.25	150 W	9	ANSI/AAMI ES 60601-1: 2005	20B	0	1
SMM400PD26-XE0275A@(1)											
	100-240ac	47-63	0	24.75(a)	18.8(a)	419.92(a)	9	ANSI/AAMI ES 60601-1: 2005	20B	0	1
				51.68(a)	11.3(a)	455.4(a)	9				

	100-240ac	50-60	0	10.5	0.10-0.76	8	9	60601-1	20B	0	2
VEP08US12-xy (a)											
	100-240ac	50-60	0	12	0.10-0.66	8	9	60601-1	20B	0	2
VEP08US125-xy (a)											
	100-240ac	50-60	0	12.5	0.10-0.64	8	9	60601-1	20B	0	2
VEP08US138-xy (a)											
	100-240ac	50-60	0	13.8	0.10-0.57	8	9	60601-1	20B	0	2
VEP08US15-xy (a)											
	100-240ac	50-60	0	15	0.10-0.53	8	9	60601-1	20B	0	2
VEP08US18-xy (a)											
	100-240ac	50-60	0	18	0.10-0.44	8	9	60601-1	20B	0	2

[*r] - Output values are rated.

(#) - All models followed by alphanumeric characters

(1) - (a) - With fan(22.95CFM FAN).

(2) - (b) - Without fan.

(a) - Where x & y can be blank or 0-9 or A-Z to indicate alternative output connectors.

(b) - Where x =03, 05, 15, 18, 24, 27, 36, 48, 54, where y= blank, (without fan), A (u-case + top cover)(with fan) or C (for enclosure) and where z = blank, 0 - 9 or any alphanumeric characters for marketing purposes

(c) - Where x= 21, 22, 23, 24, 25, where y= blank, (without fan), A (u-case + top cover)(with fan) or C (for enclosure) and where zzzz denotes blank, 0-9 incl. or any alphanumeric characters for marketing purposes

(d) - Y denotes any alpha numeric character or blank, and S may be an S or blank.

(e) - Y = 0-9, A-Z or blank, Z = S, Blank or PF.

(f) - Y= A-Z, 0-9 or blank, Z = blank, 0-9 or any alphanumeric characters for marketing purposes

(h) - yy = 0- 9, A-Z and blank, z= blank, E or F

(i) - y = B or C

* - Where y= A-Z, 0-9 incl., hyphen or blank.

@ - Product certified to ANSI/AAMI ES 60601-1: 2005; CAN/CSA-C22.2 No. 60601-1:08.

a - X=1, stands for Class II products

b - X=2/3, stands for Class I products

c - XXX:090-270, stands for output voltage from 9V to 27Vdc. YYY:010-500, stands for output current from 0.1 to 5.0A

d - XXX:090-240, stands for output voltage from 9V to 27Vdc. YYY:010-402, stands for output current form 0.10 to 4.02A

e - YYY:010-200, stands for output current from 0.10-2.00A

Note - All models may be followed by two additional alphanumeric characters.

X - can be any alphanumeric or blank for different client identification

[+] - x may be blank or any alpha character A-Z

[@] - y may be blank or any numeric character 0-9

[g] - Where X can be blank, A-Z or 0-9

[r] - Output values are rated

[s] - May be followed by -SG01

Marking: Company name and model designation.

Last Updated on 2013-08-01

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2013 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up

Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2013 UL LLC".