



Product Service

CERTIFICATE

No. Z1 16 01 65969 172

Holder of Certificate: **XP Power Limited**
401 Commonwealth Drive,
Haw Par Technocentre, Lobby B, #02-02 149598
SINGAPORE

Production Facility(ies): 73018

Certification Mark:



Product: **Adaptors
(AC Adapter)**

Model(s): VEL30USxxx-zz-JA-H, VEL30USxxx-zz-JA, VER30USxxx-JA,
VET30USxxxC2-JA, VEL36USxxx-zz-JA-H, VEL36USxxx-zz-JA,
VER36USxxx-JA, VET36USxxxC2-JA
(XXX, zz are variables, See page 2-9 for details)

Parameters:

Rated Input :	100-240VAC or 200-240VAC, 50/60Hz, 0.8A
Rated Output :	See page 2-9 for details
Protection Class :	II
Degree of Protection :	IP20

Tested according to: BS EN 60950-1:2006/A2:2013
BS EN 60065:2002/A12:2011

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.


Test report no.: 64210150147901A

Valid until: 2017-01-14

Date, 2016-01-26


(Richard Zhu)

Page 1 of 9



CERTIFICATE
No. Z1 16 01 65969 172



Product Service

Model Number	Rated Output Voltage (V.d.c.)	Rated Output Current (mA)
For model: VEL30USxxx-zz-JA-H, VEL30USxxx-zz-JA, VER30USxxx-JA, VET30USxxxC2-JA		
VEL30US090-zz-JA-H, VEL30US090-zz-JA, VER30US090-JA, VET30US090C2-JA	9.0	3330
VEL30US091-zz-JA-H, VEL30US091-zz-JA, VER30US091-JA, VET30US091C2-JA	9.1	3300
VEL30US092-zz-JA-H, VEL30US092-zz-JA, VER30US092-JA, VET30US092C2-JA	9.2	3260
VEL30US093-zz-JA-H, VEL30US093-zz-JA, VER30US093-JA, VET30US093C2-JA	9.3	3230
VEL30US094-zz-JA-H, VEL30US094-zz-JA, VER30US094-JA, VET30US094C2-JA	9.4	3190
VEL30US095-zz-JA-H, VEL30US095-zz-JA, VER30US095-JA, VET30US095C2-JA	9.5	3160
VEL30US096-zz-JA-H, VEL30US096-zz-JA, VER30US096-JA, VET30US096C2-JA	9.6	3130
VEL30US097-zz-JA-H, VEL30US097-zz-JA, VER30US097-JA, VET30US097C2-JA	9.7	3090
VEL30US098-zz-JA-H, VEL30US098-zz-JA, VER30US098-JA, VET30US098C2-JA	9.8	3060
VEL30US099-zz-JA-H, VEL30US099-zz-JA, VER30US099-JA, VET30US099C2-JA	9.9	3030
VEL30US100-zz-JA-H, VEL30US100-zz-JA, VER30US100-JA, VET30US100C2-JA	10.0	3000
VEL30US101-zz-JA-H, VEL30US101-zz-JA, VER30US101-JA, VET30US101C2-JA	10.1	2970
VEL30US102-zz-JA-H, VEL30US102-zz-JA, VER30US102-JA, VET30US102C2-JA	10.2	2940
VEL30US103-zz-JA-H, VEL30US103-zz-JA, VER30US103-JA, VET30US103C2-JA	10.3	2910
VEL30US104-zz-JA-H, VEL30US104-zz-JA, VER30US104-JA, VET30US104C2-JA	10.4	2890
VEL30US105-zz-JA-H, VEL30US105-zz-JA, VER30US105-JA, VET30US105C2-JA	10.5	2860
VEL30US106-zz-JA-H, VEL30US106-zz-JA, VER30US106-JA, VET30US106C2-JA	10.6	2830
VEL30US107-zz-JA-H, VEL30US107-zz-JA, VER30US107-JA, VET30US107C2-JA	10.7	2800
VEL30US108-zz-JA-H, VEL30US108-zz-JA, VER30US108-JA, VET30US108C2-JA	10.8	2780
VEL30US109-zz-JA-H, VEL30US109-zz-JA, VER30US109-JA, VET30US109C2-JA	10.9	2750
VEL30US110-zz-JA-H, VEL30US110-zz-JA, VER30US110-JA, VET30US110C2-JA	11.0	2730
VEL30US111-zz-JA-H, VEL30US111-zz-JA, VER30US111-JA, VET30US111C2-JA	11.1	2700
VEL30US112-zz-JA-H, VEL30US112-zz-JA, VER30US112-JA, VET30US112C2-JA	11.2	2680
VEL30US113-zz-JA-H, VEL30US113-zz-JA, VER30US113-JA, VET30US113C2-JA	11.3	2660
VEL30US114-zz-JA-H, VEL30US114-zz-JA, VER30US114-JA, VET30US114C2-JA	11.4	2630
VEL30US115-zz-JA-H, VEL30US115-zz-JA, VER30US115-JA, VET30US115C2-JA	11.5	2610

CERTIFICATE
No. Z1 16 01 65969 172



Product Service

VEL30US116-zz-JA-H, VEL30US116-zz-JA, VER30US116-JA, VET30US116C2-JA	11.6	2590
VEL30US117-zz-JA-H, VEL30US117-zz-JA, VER30US117-JA, VET30US117C2-JA	11.7	2560
VEL30US118-zz-JA-H, VEL30US118-zz-JA, VER30US118-JA, VET30US118C2-JA	11.8	2540
VEL30US119-zz-JA-H, VEL30US119-zz-JA, VER30US119-JA, VET30US119C2-JA	11.9	2520
VEL30US120-zz-JA-H, VEL30US120-zz-JA, VER30US120-JA, VET30US120C2-JA	12.0	2500
VEL30US121-zz-JA-H, VEL30US121-zz-JA, VER30US121-JA, VET30US121C2-JA	12.1	2480
VEL30US122-zz-JA-H, VEL30US122-zz-JA, VER30US122-JA, VET30US122C2-JA	12.2	2460
VEL30US123-zz-JA-H, VEL30US123-zz-JA, VER30US123-JA, VET30US123C2-JA	12.3	2440
VEL30US124-zz-JA-H, VEL30US124-zz-JA, VER30US124-JA, VET30US124C2-JA	12.4	2420
VEL30US125-zz-JA-H, VEL30US125-zz-JA, VER30US125-JA, VET30US125C2-JA	12.5	2400
VEL30US126-zz-JA-H, VEL30US126-zz-JA, VER30US126-JA, VET30US126C2-JA	12.6	2380
VEL30US127-zz-JA-H, VEL30US127-zz-JA, VER30US127-JA, VET30US127C2-JA	12.7	2360
VEL30US128-zz-JA-H, VEL30US128-zz-JA, VER30US128-JA, VET30US128C2-JA	12.8	2340
VEL30US129-zz-JA-H, VEL30US129-zz-JA, VER30US129-JA, VET30US129C2-JA	12.9	2330
VEL30US130-zz-JA-H, VEL30US130-zz-JA, VER30US130-JA, VET30US130C2-JA	13.0	2310
VEL30US131-zz-JA-H, VEL30US131-zz-JA, VER30US131-JA, VET30US131C2-JA	13.1	2290
VEL30US132-zz-JA-H, VEL30US132-zz-JA, VER30US132-JA, VET30US132C2-JA	13.2	2270
VEL30US133-zz-JA-H, VEL30US133-zz-JA, VER30US133-JA, VET30US133C2-JA	13.3	2260
VEL30US134-zz-JA-H, VEL30US134-zz-JA, VER30US134-JA, VET30US134C2-JA	13.4	2240
VEL30US135-zz-JA-H, VEL30US135-zz-JA, VER30US135-JA, VET30US135C2-JA	13.5	2220
VEL30US136-zz-JA-H, VEL30US136-zz-JA, VER30US136-JA, VET30US136C2-JA	13.6	2210
VEL30US137-zz-JA-H, VEL30US137-zz-JA, VER30US137-JA, VET30US137C2-JA	13.7	2190
VEL30US138-zz-JA-H, VEL30US138-zz-JA, VER30US138-JA, VET30US138C2-JA	13.8	2170
VEL30US139-zz-JA-H, VEL30US139-zz-JA, VER30US139-JA, VET30US139C2-JA	13.9	2160
VEL30US140-zz-JA-H, VEL30US140-zz-JA, VER30US140-JA, VET30US140C2-JA	14.0	2140
VEL30US141-zz-JA-H, VEL30US141-zz-JA, VER30US141-JA, VET30US141C2-JA	14.1	2130
VEL30US142-zz-JA-H, VEL30US142-zz-JA, VER30US142-JA, VET30US142C2-JA	14.2	2110
VEL30US143-zz-JA-H, VEL30US143-zz-JA, VER30US143-JA, VET30US143C2-JA	14.3	2100

CERTIFICATE
No. Z1 16 01 65969 172



Product Service

VEL30US144-zz-JA-H, VEL30US144-zz-JA, VER30US144-JA, VET30US144C2-JA	14.4	2080
VEL30US145-zz-JA-H, VEL30US145-zz-JA, VER30US145-JA, VET30US145C2-JA	14.5	2070
VEL30US146-zz-JA-H, VEL30US146-zz-JA, VER30US146-JA, VET30US146C2-JA	14.6	2060
VEL30US147-zz-JA-H, VEL30US147-zz-JA, VER30US147-JA, VET30US147C2-JA	14.7	2040
VEL30US148-zz-JA-H, VEL30US148-zz-JA, VER30US148-JA, VET30US148C2-JA	14.8	2030
VEL30US149-zz-JA-H, VEL30US149-zz-JA, VER30US149-JA, VET30US149C2-JA	14.9	2010
VEL30US150-zz-JA-H, VEL30US150-zz-JA, VER30US150-JA, VET30US150C2-JA	15.0	2000
VEL30US180-zz-JA-H, VEL30US180-zz-JA, VER30US180-JA, VET30US180C2-JA	18.0	1670
VEL30US181-zz-JA-H, VEL30US181-zz-JA, VER30US181-JA, VET30US181C2-JA	18.1	1660
VEL30US182-zz-JA-H, VEL30US182-zz-JA, VER30US182-JA, VET30US182C2-JA	18.2	1650
VEL30US183-zz-JA-H, VEL30US183-zz-JA, VER30US183-JA, VET30US183C2-JA	18.3	1640
VEL30US184-zz-JA-H, VEL30US184-zz-JA, VER30US184-JA, VET30US184C2-JA	18.4	1630
VEL30US185-zz-JA-H, VEL30US185-zz-JA, VER30US185-JA, VET30US185C2-JA	18.5	1620
VEL30US186-zz-JA-H, VEL30US186-zz-JA, VER30US186-JA, VET30US186C2-JA	18.6	1610
VEL30US187-zz-JA-H, VEL30US187-zz-JA, VER30US187-JA, VET30US187C2-JA	18.7	1600
VEL30US188-zz-JA-H, VEL30US188-zz-JA, VER30US188-JA, VET30US188C2-JA	18.8	1600
VEL30US189-zz-JA-H, VEL30US189-zz-JA, VER30US189-JA, VET30US189C2-JA	18.9	1590
VEL30US190-zz-JA-H, VEL30US190-zz-JA, VER30US190-JA, VET30US190C2-JA	19.0	1580
VEL30US191-zz-JA-H, VEL30US191-zz-JA, VER30US191-JA, VET30US191C2-JA	19.1	1570
VEL30US192-zz-JA-H, VEL30US192-zz-JA, VER30US192-JA, VET30US192C2-JA	19.2	1560
VEL30US193-zz-JA-H, VEL30US193-zz-JA, VER30US193-JA, VET30US193C2-JA	19.3	1550
VEL30US194-zz-JA-H, VEL30US194-zz-JA, VER30US194-JA, VET30US194C2-JA	19.4	1550
VEL30US195-zz-JA-H, VEL30US195-zz-JA, VER30US195-JA, VET30US195C2-JA	19.5	1540
VEL30US196-zz-JA-H, VEL30US196-zz-JA, VER30US196-JA, VET30US196C2-JA	19.6	1530
VEL30US197-zz-JA-H, VEL30US197-zz-JA, VER30US197-JA, VET30US197C2-JA	19.7	1520
VEL30US198-zz-JA-H, VEL30US198-zz-JA, VER30US198-JA, VET30US198C2-JA	19.8	1520
VEL30US199-zz-JA-H, VEL30US199-zz-JA, VER30US199-JA, VET30US199C2-JA	19.9	1510
VEL30US200-zz-JA-H, VEL30US200-zz-JA, VER30US200-JA, VET30US200C2-JA	20.0	1500

CERTIFICATE
No. Z1 16 01 65969 172



Product Service

VEL30US201-zz-JA-H, VEL30US201-zz-JA, VER30US201-JA, VET30US201C2-JA	20.1	1490
VEL30US202-zz-JA-H, VEL30US202-zz-JA, VER30US202-JA, VET30US202C2-JA	20.2	1490
VEL30US203-zz-JA-H, VEL30US203-zz-JA, VER30US203-JA, VET30US203C2-JA	20.3	1480
VEL30US204-zz-JA-H, VEL30US204-zz-JA, VER30US204-JA, VET30US204C2-JA	20.4	1470
VEL30US205-zz-JA-H, VEL30US205-zz-JA, VER30US205-JA, VET30US205C2-JA	20.5	1460
VEL30US206-zz-JA-H, VEL30US206-zz-JA, VER30US206-JA, VET30US206C2-JA	20.6	1460
VEL30US207-zz-JA-H, VEL30US207-zz-JA, VER30US207-JA, VET30US207C2-JA	20.7	1450
VEL30US208-zz-JA-H, VEL30US208-zz-JA, VER30US208-JA, VET30US208C2-JA	20.8	1440
VEL30US209-zz-JA-H, VEL30US209-zz-JA, VER30US209-JA, VET30US209C2-JA	20.9	1440
VEL30US210-zz-JA-H, VEL30US210-zz-JA, VER30US210-JA, VET30US210C2-JA	21.0	1430
VEL30US211-zz-JA-H, VEL30US211-zz-JA, VER30US211-JA, VET30US211C2-JA	21.1	1420
VEL30US212-zz-JA-H, VEL30US212-zz-JA, VER30US212-JA, VET30US212C2-JA	21.2	1420
VEL30US213-zz-JA-H, VEL30US213-zz-JA, VER30US213-JA, VET30US213C2-JA	21.3	1410
VEL30US214-zz-JA-H, VEL30US214-zz-JA, VER30US214-JA, VET30US214C2-JA	21.4	1400
VEL30US215-zz-JA-H, VEL30US215-zz-JA, VER30US215-JA, VET30US215C2-JA	21.5	1400
VEL30US216-zz-JA-H, VEL30US216-zz-JA, VER30US216-JA, VET30US216C2-JA	21.6	1390
VEL30US217-zz-JA-H, VEL30US217-zz-JA, VER30US217-JA, VET30US217C2-JA	21.7	1380
VEL30US218-zz-JA-H, VEL30US218-zz-JA, VER30US218-JA, VET30US218C2-JA	21.8	1380
VEL30US219-zz-JA-H, VEL30US219-zz-JA, VER30US219-JA, VET30US219C2-JA	21.9	1370
VEL30US220-zz-JA-H, VEL30US220-zz-JA, VER30US220-JA, VET30US220C2-JA	22.0	1360
VEL30US221-zz-JA-H, VEL30US221-zz-JA, VER30US221-JA, VET30US221C2-JA	22.1	1360
VEL30US222-zz-JA-H, VEL30US222-zz-JA, VER30US222-JA, VET30US222C2-JA	22.2	1350
VEL30US223-zz-JA-H, VEL30US223-zz-JA, VER30US223-JA, VET30US223C2-JA	22.3	1350
VEL30US224-zz-JA-H, VEL30US224-zz-JA, VER30US224-JA, VET30US224C2-JA	22.4	1340
VEL30US225-zz-JA-H, VEL30US225-zz-JA, VER30US225-JA, VET30US225C2-JA	22.5	1330
VEL30US226-zz-JA-H, VEL30US226-zz-JA, VER30US226-JA, VET30US226C2-JA	22.6	1330
VEL30US227-zz-JA-H, VEL30US227-zz-JA, VER30US227-JA, VET30US227C2-JA	22.7	1320
VEL30US228-zz-JA-H, VEL30US228-zz-JA, VER30US228-JA, VET30US228C2-JA	22.8	1320

CERTIFICATE
No. Z1 16 01 65969 172



Product Service

VEL30US229-zz-JA-H, VEL30US229-zz-JA, VER30US229-JA, VET30US229C2-JA	22.9	1310
VEL30US230-zz-JA-H, VEL30US230-zz-JA, VER30US230-JA, VET30US230C2-JA	23.0	1300
VEL30US231-zz-JA-H, VEL30US231-zz-JA, VER30US231-JA, VET30US231C2-JA	23.1	1300
VEL30US232-zz-JA-H, VEL30US232-zz-JA, VER30US232-JA, VET30US232C2-JA	23.2	1290
VEL30US233-zz-JA-H, VEL30US233-zz-JA, VER30US233-JA, VET30US233C2-JA	23.3	1290
VEL30US234-zz-JA-H, VEL30US234-zz-JA, VER30US234-JA, VET30US234C2-JA	23.4	1280
VEL30US235-zz-JA-H, VEL30US235-zz-JA, VER30US235-JA, VET30US235C2-JA	23.5	1280
VEL30US236-zz-JA-H, VEL30US236-zz-JA, VER30US236-JA, VET30US236C2-JA	23.6	1270
VEL30US237-zz-JA-H, VEL30US237-zz-JA, VER30US237-JA, VET30US237C2-JA	23.7	1270
VEL30US238-zz-JA-H, VEL30US238-zz-JA, VER30US238-JA, VET30US238C2-JA	23.8	1260
VEL30US239-zz-JA-H, VEL30US239-zz-JA, VER30US239-JA, VET30US239C2-JA	23.9	1260
VEL30US240-zz-JA-H, VEL30US240-zz-JA, VER30US240-JA, VET30US240C2-JA	24.0	1250
For model: VEL36USxxx-zz-JA-H, VEL36USxxx-zz-JA, VER36USxxx-JA, VET36USxxxC2-JA		
VEL36US120-zz-JA-H, VEL36US120-zz-JA, VER36US120-JA, VET36US120C2-JA	12.0	3000
VEL36US121-zz-JA-H, VEL36US121-zz-JA, VER36US121-JA, VET36US121C2-JA	12.1	2970
VEL36US122-zz-JA-H, VEL36US122-zz-JA, VER36US122-JA, VET36US122C2-JA	12.2	2950
VEL36US123-zz-JA-H, VEL36US123-zz-JA, VER36US123-JA, VET36US123C2-JA	12.3	2920
VEL36US124-zz-JA-H, VEL36US124-zz-JA, VER36US124-JA, VET36US124C2-JA	12.4	2900
VEL36US125-zz-JA-H, VEL36US125-zz-JA, VER36US125-JA, VET36US125C2-JA	12.5	2880
VEL36US126-zz-JA-H, VEL36US126-zz-JA, VER36US126-JA, VET36US126C2-JA	12.6	2850
VEL36US127-zz-JA-H, VEL36US127-zz-JA, VER36US127-JA, VET36US127C2-JA	12.7	2830
VEL36US128-zz-JA-H, VEL36US128-zz-JA, VER36US128-JA, VET36US128C2-JA	12.8	2810
VEL36US129-zz-JA-H, VEL36US129-zz-JA, VER36US129-JA, VET36US129C2-JA	12.9	2790
VEL36US130-zz-JA-H, VEL36US130-zz-JA, VER36US130-JA, VET36US130C2-JA	13.0	2760
VEL36US131-zz-JA-H, VEL36US131-zz-JA, VER36US131-JA, VET36US131C2-JA	13.1	2740
VEL36US132-zz-JA-H, VEL36US132-zz-JA, VER36US132-JA, VET36US132C2-JA	13.2	2720
VEL36US133-zz-JA-H, VEL36US133-zz-JA, VER36US133-JA, VET36US133C2-JA	13.3	2700
VEL36US134-zz-JA-H, VEL36US134-zz-JA, VER36US134-JA, VET36US134C2-JA	13.4	2680

CERTIFICATE
No. Z1 16 01 65969 172



Product Service

VEL36US135-zz-JA-H, VEL36US135-zz-JA, VER36US135-JA, VET36US135C2-JA	13.5	2660
VEL36US136-zz-JA-H, VEL36US136-zz-JA, VER36US136-JA, VET36US136C2-JA	13.6	2640
VEL36US137-zz-JA-H, VEL36US137-zz-JA, VER36US137-JA, VET36US137C2-JA	13.7	2620
VEL36US138-zz-JA-H, VEL36US138-zz-JA, VER36US138-JA, VET36US138C2-JA	13.8	2600
VEL36US139-zz-JA-H, VEL36US139-zz-JA, VER36US139-JA, VET36US139C2-JA	13.9	2580
VEL36US140-zz-JA-H, VEL36US140-zz-JA, VER36US140-JA, VET36US140C2-JA	14.0	2570
VEL36US141-zz-JA-H, VEL36US141-zz-JA, VER36US141-JA, VET36US141C2-JA	14.1	2550
VEL36US142-zz-JA-H, VEL36US142-zz-JA, VER36US142-JA, VET36US142C2-JA	14.2	2530
VEL36US143-zz-JA-H, VEL36US143-zz-JA, VER36US143-JA, VET36US143C2-JA	14.3	2510
VEL36US144-zz-JA-H, VEL36US144-zz-JA, VER36US144-JA, VET36US144C2-JA	14.4	2500
VEL36US145-zz-JA-H, VEL36US145-zz-JA, VER36US145-JA, VET36US145C2-JA	14.5	2480
VEL36US146-zz-JA-H, VEL36US146-zz-JA, VER36US146-JA, VET36US146C2-JA	14.6	2460
VEL36US147-zz-JA-H, VEL36US147-zz-JA, VER36US147-JA, VET36US147C2-JA	14.7	2440
VEL36US148-zz-JA-H, VEL36US148-zz-JA, VER36US148-JA, VET36US148C2-JA	14.8	2430
VEL36US149-zz-JA-H, VEL36US149-zz-JA, VER36US149-JA, VET36US149C2-JA	14.9	2410
VEL36US150-zz-JA-H, VEL36US150-zz-JA, VER36US150-JA, VET36US150C2-JA	15.0	2400
VEL36US180-zz-JA-H, VEL36US180-zz-JA, VER36US180-JA, VET36US180C2-JA	18.0	2000
VEL36US181-zz-JA-H, VEL36US181-zz-JA, VER36US181-JA, VET36US181C2-JA	18.1	1980
VEL36US182-zz-JA-H, VEL36US182-zz-JA, VER36US182-JA, VET36US182C2-JA	18.2	1970
VEL36US183-zz-JA-H, VEL36US183-zz-JA, VER36US183-JA, VET36US183C2-JA	18.3	1960
VEL36US184-zz-JA-H, VEL36US184-zz-JA, VER36US184-JA, VET36US184C2-JA	18.4	1940
VEL36US185-zz-JA-H, VEL36US185-zz-JA, VER36US185-JA, VET36US185C2-JA	18.5	1940
VEL36US186-zz-JA-H, VEL36US186-zz-JA, VER36US186-JA, VET36US186C2-JA	18.6	1930
VEL36US187-zz-JA-H, VEL36US187-zz-JA, VER36US187-JA, VET36US187C2-JA	18.7	1920
VEL36US188-zz-JA-H, VEL36US188-zz-JA, VER36US188-JA, VET36US188C2-JA	18.8	1910
VEL36US189-zz-JA-H, VEL36US189-zz-JA, VER36US189-JA, VET36US189C2-JA	18.9	1900
VEL36US190-zz-JA-H, VEL36US190-zz-JA, VER36US190-JA, VET36US190C2-JA	19.0	1890
VEL36US191-zz-JA-H, VEL36US191-zz-JA, VER36US191-JA, VET36US191C2-JA	19.1	1880

CERTIFICATE
No. Z1 16 01 65969 172



Product Service

VEL36US192-zz-JA-H, VEL36US192-zz-JA, VER36US192-JA, VET36US192C2-JA	19.2	1870
VEL36US193-zz-JA-H, VEL36US193-zz-JA, VER36US193-JA, VET36US193C2-JA	19.3	1860
VEL36US194-zz-JA-H, VEL36US194-zz-JA, VER36US194-JA, VET36US194C2-JA	19.4	1850
VEL36US195-zz-JA-H, VEL36US195-zz-JA, VER36US195-JA, VET36US195C2-JA	19.5	1840
VEL36US196-zz-JA-H, VEL36US196-zz-JA, VER36US196-JA, VET36US196C2-JA	19.6	1830
VEL36US197-zz-JA-H, VEL36US197-zz-JA, VER36US197-JA, VET36US197C2-JA	19.7	1820
VEL36US198-zz-JA-H, VEL36US198-zz-JA, VER36US198-JA, VET36US198C2-JA	19.8	1810
VEL36US199-zz-JA-H, VEL36US199-zz-JA, VER36US199-JA, VET36US199C2-JA	19.9	1800
VEL36US200-zz-JA-H, VEL36US200-zz-JA, VER36US200-JA, VET36US200C2-JA	20.0	1800
VEL36US201-zz-JA-H, VEL36US201-zz-JA, VER36US201-JA, VET36US201C2-JA	20.1	1790
VEL36US202-zz-JA-H, VEL36US202-zz-JA, VER36US202-JA, VET36US202C2-JA	20.2	1780
VEL36US203-zz-JA-H, VEL36US203-zz-JA, VER36US203-JA, VET36US203C2-JA	20.3	1770
VEL36US204-zz-JA-H, VEL36US204-zz-JA, VER36US204-JA, VET36US204C2-JA	20.4	1760
VEL36US205-zz-JA-H, VEL36US205-zz-JA, VER36US205-JA, VET36US205C2-JA	20.5	1750
VEL36US206-zz-JA-H, VEL36US206-zz-JA, VER36US206-JA, VET36US206C2-JA	20.6	1730
VEL36US207-zz-JA-H, VEL36US207-zz-JA, VER36US207-JA, VET36US207C2-JA	20.7	1730
VEL36US208-zz-JA-H, VEL36US208-zz-JA, VER36US208-JA, VET36US208C2-JA	20.8	1730
VEL36US209-zz-JA-H, VEL36US209-zz-JA, VER36US209-JA, VET36US209C2-JA	20.9	1720
VEL36US210-zz-JA-H, VEL36US210-zz-JA, VER36US210-JA, VET36US210C2-JA	21.0	1710
VEL36US211-zz-JA-H, VEL36US211-zz-JA, VER36US211-JA, VET36US211C2-JA	21.1	1690
VEL36US212-zz-JA-H, VEL36US212-zz-JA, VER36US212-JA, VET36US212C2-JA	21.2	1690
VEL36US213-zz-JA-H, VEL36US213-zz-JA, VER36US213-JA, VET36US213C2-JA	21.3	1690
VEL36US214-zz-JA-H, VEL36US214-zz-JA, VER36US214-JA, VET36US214C2-JA	21.4	1680
VEL36US215-zz-JA-H, VEL36US215-zz-JA, VER36US215-JA, VET36US215C2-JA	21.5	1670
VEL36US216-zz-JA-H, VEL36US216-zz-JA, VER36US216-JA, VET36US216C2-JA	21.6	1660
VEL36US217-zz-JA-H, VEL36US217-zz-JA, VER36US217-JA, VET36US217C2-JA	21.7	1650
VEL36US218-zz-JA-H, VEL36US218-zz-JA, VER36US218-JA, VET36US218C2-JA	21.8	1650
VEL36US219-zz-JA-H, VEL36US219-zz-JA, VER36US219-JA, VET36US219C2-JA	21.9	1640

CERTIFICATE
No. Z1 16 01 65969 172



Product Service

VEL36US220-zz-JA-H, VEL36US220-zz-JA, VER36US220-JA, VET36US220C2-JA	22.0	1630
VEL36US221-zz-JA-H, VEL36US221-zz-JA, VER36US221-JA, VET36US221C2-JA	22.1	1620
VEL36US222-zz-JA-H, VEL36US222-zz-JA, VER36US222-JA, VET36US222C2-JA	22.2	1620
VEL36US223-zz-JA-H, VEL36US223-zz-JA, VER36US223-JA, VET36US223C2-JA	22.3	1610
VEL36US224-zz-JA-H, VEL36US224-zz-JA, VER36US224-JA, VET36US224C2-JA	22.4	1600
VEL36US225-zz-JA-H, VEL36US225-zz-JA, VER36US225-JA, VET36US225C2-JA	22.5	1600
VEL36US226-zz-JA-H, VEL36US226-zz-JA, VER36US226-JA, VET36US226C2-JA	22.6	1590
VEL36US227-zz-JA-H, VEL36US227-zz-JA, VER36US227-JA, VET36US227C2-JA	22.7	1580
VEL36US228-zz-JA-H, VEL36US228-zz-JA, VER36US228-JA, VET36US228C2-JA	22.8	1570
VEL36US229-zz-JA-H, VEL36US229-zz-JA, VER36US229-JA, VET36US229C2-JA	22.9	1570
VEL36US230-zz-JA-H, VEL36US230-zz-JA, VER36US230-JA, VET36US230C2-JA	23.0	1560
VEL36US231-zz-JA-H, VEL36US231-zz-JA, VER36US231-JA, VET36US231C2-JA	23.1	1550
VEL36US232-zz-JA-H, VEL36US232-zz-JA, VER36US232-JA, VET36US232C2-JA	23.2	1550
VEL36US233-zz-JA-H, VEL36US233-zz-JA, VER36US233-JA, VET36US233C2-JA	23.3	1540
VEL36US234-zz-JA-H, VEL36US234-zz-JA, VER36US234-JA, VET36US234C2-JA	23.4	1530
VEL36US235-zz-JA-H, VEL36US235-zz-JA, VER36US235-JA, VET36US235C2-JA	23.5	1530
VEL36US236-zz-JA-H, VEL36US236-zz-JA, VER36US236-JA, VET36US236C2-JA	23.6	1520
VEL36US237-zz-JA-H, VEL36US237-zz-JA, VER36US237-JA, VET36US237C2-JA	23.7	1510
VEL36US238-zz-JA-H, VEL36US238-zz-JA, VER36US238-JA, VET36US238C2-JA	23.8	1510
VEL36US239-zz-JA-H, VEL36US239-zz-JA, VER36US239-JA, VET36US239C2-JA	23.9	1500
VEL36US240-zz-JA-H, VEL36US240-zz-JA, VER36US240-JA, VET36US240C2-JA	24.0	1500

Notes:

1. xxx = 090-150, 180-240 denotes rated output voltage from 9.0-15.0V, 18.0-24.0V with step 0.1V;
2. zz = EU, UK denotes different plug type:
 - a. zz= EU, for Europe plug,
 - b. zz= UK, for United Kingdom plug.



Product Service

CERTIFICATE

No. Z1A 16 01 65969 171

Holder of Certificate: **XP Power Limited**
401 Commonwealth Drive,
Haw Par Technocentre, Lobby B, #02-02 149598
SINGAPORE

Factory(ies): 73018

Certification Mark:



Product: **Adaptors
(AC Adapter)**

Model(s): VEL30USxxx-zz-JA-H, VEL30USxxx-zz-JA, VER30USxxx-JA,
VET30USxxxC2-JA, VEL36USxxx-zz-JA-H, VEL36USxxx-zz-JA,
VER36USxxx-JA, VET36USxxxC2-JA
(XXX, zz are variables, See page 2-9 for details)

Parameters:

Rated Input :	100-240VAC or 200-240VAC, 50/60Hz, 0.8A
Rated Output :	See page 2-9 for details
Protection Class :	II
Degree of Protection :	IP20

Tested according to: EN 60950-1:2006/A2:2013
EN 60065:2002/A12:2011
AfPS GS 2014:01 PAK 3.1

The product meets the safety and health requirements of the German Product Safety Act section 20 to 22 ProdSG. The certification marks shown above can be affixed on the product. It is not permitted to alter the certification marks in any way. In addition the certificate holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. See also notes overleaf.

Test report no.: 64210150147901A

Valid until: 2017-01-14

Date, 2016-01-26


(Richard Zhu)



Page 1 of 9

CERTIFICATE
No. Z1A 16 01 65969 171



Product Service

Model Number	Rated Output Voltage (Vd.c.)	Rated Output Current (mA)
For model: VEL30USxxx-zz-JA-H, VEL30USxxx-zz-JA, VER30USxxx-JA, VET30USxxxC2-JA		
VEL30US090-zz-JA-H, VEL30US090-zz-JA, VER30US090-JA, VET30US090C2-JA	9.0	3330
VEL30US091-zz-JA-H, VEL30US091-zz-JA, VER30US091-JA, VET30US091C2-JA	9.1	3300
VEL30US092-zz-JA-H, VEL30US092-zz-JA, VER30US092-JA, VET30US092C2-JA	9.2	3260
VEL30US093-zz-JA-H, VEL30US093-zz-JA, VER30US093-JA, VET30US093C2-JA	9.3	3230
VEL30US094-zz-JA-H, VEL30US094-zz-JA, VER30US094-JA, VET30US094C2-JA	9.4	3190
VEL30US095-zz-JA-H, VEL30US095-zz-JA, VER30US095-JA, VET30US095C2-JA	9.5	3160
VEL30US096-zz-JA-H, VEL30US096-zz-JA, VER30US096-JA, VET30US096C2-JA	9.6	3130
VEL30US097-zz-JA-H, VEL30US097-zz-JA, VER30US097-JA, VET30US097C2-JA	9.7	3090
VEL30US098-zz-JA-H, VEL30US098-zz-JA, VER30US098-JA, VET30US098C2-JA	9.8	3060
VEL30US099-zz-JA-H, VEL30US099-zz-JA, VER30US099-JA, VET30US099C2-JA	9.9	3030
VEL30US100-zz-JA-H, VEL30US100-zz-JA, VER30US100-JA, VET30US100C2-JA	10.0	3000
VEL30US101-zz-JA-H, VEL30US101-zz-JA, VER30US101-JA, VET30US101C2-JA	10.1	2970
VEL30US102-zz-JA-H, VEL30US102-zz-JA, VER30US102-JA, VET30US102C2-JA	10.2	2940
VEL30US103-zz-JA-H, VEL30US103-zz-JA, VER30US103-JA, VET30US103C2-JA	10.3	2910
VEL30US104-zz-JA-H, VEL30US104-zz-JA, VER30US104-JA, VET30US104C2-JA	10.4	2890
VEL30US105-zz-JA-H, VEL30US105-zz-JA, VER30US105-JA, VET30US105C2-JA	10.5	2860
VEL30US106-zz-JA-H, VEL30US106-zz-JA, VER30US106-JA, VET30US106C2-JA	10.6	2830
VEL30US107-zz-JA-H, VEL30US107-zz-JA, VER30US107-JA, VET30US107C2-JA	10.7	2800
VEL30US108-zz-JA-H, VEL30US108-zz-JA, VER30US108-JA, VET30US108C2-JA	10.8	2780
VEL30US109-zz-JA-H, VEL30US109-zz-JA, VER30US109-JA, VET30US109C2-JA	10.9	2750
VEL30US110-zz-JA-H, VEL30US110-zz-JA, VER30US110-JA, VET30US110C2-JA	11.0	2730
VEL30US111-zz-JA-H, VEL30US111-zz-JA, VER30US111-JA, VET30US111C2-JA	11.1	2700
VEL30US112-zz-JA-H, VEL30US112-zz-JA, VER30US112-JA, VET30US112C2-JA	11.2	2680
VEL30US113-zz-JA-H, VEL30US113-zz-JA, VER30US113-JA, VET30US113C2-JA	11.3	2660
VEL30US114-zz-JA-H, VEL30US114-zz-JA, VER30US114-JA, VET30US114C2-JA	11.4	2630
VEL30US115-zz-JA-H, VEL30US115-zz-JA, VER30US115-JA, VET30US115C2-JA	11.5	2610

CERTIFICATE
No. Z1A 16 01 65969 171



Product Service

VEL30US116-zz-JA-H, VEL30US116-zz-JA, VER30US116-JA, VET30US116C2-JA	11.6	2590
VEL30US117-zz-JA-H, VEL30US117-zz-JA, VER30US117-JA, VET30US117C2-JA	11.7	2560
VEL30US118-zz-JA-H, VEL30US118-zz-JA, VER30US118-JA, VET30US118C2-JA	11.8	2540
VEL30US119-zz-JA-H, VEL30US119-zz-JA, VER30US119-JA, VET30US119C2-JA	11.9	2520
VEL30US120-zz-JA-H, VEL30US120-zz-JA, VER30US120-JA, VET30US120C2-JA	12.0	2500
VEL30US121-zz-JA-H, VEL30US121-zz-JA, VER30US121-JA, VET30US121C2-JA	12.1	2480
VEL30US122-zz-JA-H, VEL30US122-zz-JA, VER30US122-JA, VET30US122C2-JA	12.2	2460
VEL30US123-zz-JA-H, VEL30US123-zz-JA, VER30US123-JA, VET30US123C2-JA	12.3	2440
VEL30US124-zz-JA-H, VEL30US124-zz-JA, VER30US124-JA, VET30US124C2-JA	12.4	2420
VEL30US125-zz-JA-H, VEL30US125-zz-JA, VER30US125-JA, VET30US125C2-JA	12.5	2400
VEL30US126-zz-JA-H, VEL30US126-zz-JA, VER30US126-JA, VET30US126C2-JA	12.6	2380
VEL30US127-zz-JA-H, VEL30US127-zz-JA, VER30US127-JA, VET30US127C2-JA	12.7	2360
VEL30US128-zz-JA-H, VEL30US128-zz-JA, VER30US128-JA, VET30US128C2-JA	12.8	2340
VEL30US129-zz-JA-H, VEL30US129-zz-JA, VER30US129-JA, VET30US129C2-JA	12.9	2330
VEL30US130-zz-JA-H, VEL30US130-zz-JA, VER30US130-JA, VET30US130C2-JA	13.0	2310
VEL30US131-zz-JA-H, VEL30US131-zz-JA, VER30US131-JA, VET30US131C2-JA	13.1	2290
VEL30US132-zz-JA-H, VEL30US132-zz-JA, VER30US132-JA, VET30US132C2-JA	13.2	2270
VEL30US133-zz-JA-H, VEL30US133-zz-JA, VER30US133-JA, VET30US133C2-JA	13.3	2260
VEL30US134-zz-JA-H, VEL30US134-zz-JA, VER30US134-JA, VET30US134C2-JA	13.4	2240
VEL30US135-zz-JA-H, VEL30US135-zz-JA, VER30US135-JA, VET30US135C2-JA	13.5	2220
VEL30US136-zz-JA-H, VEL30US136-zz-JA, VER30US136-JA, VET30US136C2-JA	13.6	2210
VEL30US137-zz-JA-H, VEL30US137-zz-JA, VER30US137-JA, VET30US137C2-JA	13.7	2190
VEL30US138-zz-JA-H, VEL30US138-zz-JA, VER30US138-JA, VET30US138C2-JA	13.8	2170
VEL30US139-zz-JA-H, VEL30US139-zz-JA, VER30US139-JA, VET30US139C2-JA	13.9	2160
VEL30US140-zz-JA-H, VEL30US140-zz-JA, VER30US140-JA, VET30US140C2-JA	14.0	2140
VEL30US141-zz-JA-H, VEL30US141-zz-JA, VER30US141-JA, VET30US141C2-JA	14.1	2130
VEL30US142-zz-JA-H, VEL30US142-zz-JA, VER30US142-JA, VET30US142C2-JA	14.2	2110
VEL30US143-zz-JA-H, VEL30US143-zz-JA, VER30US143-JA, VET30US143C2-JA	14.3	2100

CERTIFICATE
No. Z1A 16 01 65969 171



Product Service

VEL30US144-zz-JA-H, VEL30US144-zz-JA, VER30US144-JA, VET30US144C2-JA	14.4	2080
VEL30US145-zz-JA-H, VEL30US145-zz-JA, VER30US145-JA, VET30US145C2-JA	14.5	2070
VEL30US146-zz-JA-H, VEL30US146-zz-JA, VER30US146-JA, VET30US146C2-JA	14.6	2060
VEL30US147-zz-JA-H, VEL30US147-zz-JA, VER30US147-JA, VET30US147C2-JA	14.7	2040
VEL30US148-zz-JA-H, VEL30US148-zz-JA, VER30US148-JA, VET30US148C2-JA	14.8	2030
VEL30US149-zz-JA-H, VEL30US149-zz-JA, VER30US149-JA, VET30US149C2-JA	14.9	2010
VEL30US150-zz-JA-H, VEL30US150-zz-JA, VER30US150-JA, VET30US150C2-JA	15.0	2000
VEL30US180-zz-JA-H, VEL30US180-zz-JA, VER30US180-JA, VET30US180C2-JA	18.0	1670
VEL30US181-zz-JA-H, VEL30US181-zz-JA, VER30US181-JA, VET30US181C2-JA	18.1	1660
VEL30US182-zz-JA-H, VEL30US182-zz-JA, VER30US182-JA, VET30US182C2-JA	18.2	1650
VEL30US183-zz-JA-H, VEL30US183-zz-JA, VER30US183-JA, VET30US183C2-JA	18.3	1640
VEL30US184-zz-JA-H, VEL30US184-zz-JA, VER30US184-JA, VET30US184C2-JA	18.4	1630
VEL30US185-zz-JA-H, VEL30US185-zz-JA, VER30US185-JA, VET30US185C2-JA	18.5	1620
VEL30US186-zz-JA-H, VEL30US186-zz-JA, VER30US186-JA, VET30US186C2-JA	18.6	1610
VEL30US187-zz-JA-H, VEL30US187-zz-JA, VER30US187-JA, VET30US187C2-JA	18.7	1600
VEL30US188-zz-JA-H, VEL30US188-zz-JA, VER30US188-JA, VET30US188C2-JA	18.8	1600
VEL30US189-zz-JA-H, VEL30US189-zz-JA, VER30US189-JA, VET30US189C2-JA	18.9	1590
VEL30US190-zz-JA-H, VEL30US190-zz-JA, VER30US190-JA, VET30US190C2-JA	19.0	1580
VEL30US191-zz-JA-H, VEL30US191-zz-JA, VER30US191-JA, VET30US191C2-JA	19.1	1570
VEL30US192-zz-JA-H, VEL30US192-zz-JA, VER30US192-JA, VET30US192C2-JA	19.2	1560
VEL30US193-zz-JA-H, VEL30US193-zz-JA, VER30US193-JA, VET30US193C2-JA	19.3	1550
VEL30US194-zz-JA-H, VEL30US194-zz-JA, VER30US194-JA, VET30US194C2-JA	19.4	1550
VEL30US195-zz-JA-H, VEL30US195-zz-JA, VER30US195-JA, VET30US195C2-JA	19.5	1540
VEL30US196-zz-JA-H, VEL30US196-zz-JA, VER30US196-JA, VET30US196C2-JA	19.6	1530
VEL30US197-zz-JA-H, VEL30US197-zz-JA, VER30US197-JA, VET30US197C2-JA	19.7	1520
VEL30US198-zz-JA-H, VEL30US198-zz-JA, VER30US198-JA, VET30US198C2-JA	19.8	1520
VEL30US199-zz-JA-H, VEL30US199-zz-JA, VER30US199-JA, VET30US199C2-JA	19.9	1510
VEL30US200-zz-JA-H, VEL30US200-zz-JA, VER30US200-JA, VET30US200C2-JA	20.0	1500

CERTIFICATE
No. Z1A 16 01 65969 171



Product Service

VEL30US201-zz-JA-H, VEL30US201-zz-JA, VER30US201-JA, VET30US201C2-JA	20.1	1490
VEL30US202-zz-JA-H, VEL30US202-zz-JA, VER30US202-JA, VET30US202C2-JA	20.2	1490
VEL30US203-zz-JA-H, VEL30US203-zz-JA, VER30US203-JA, VET30US203C2-JA	20.3	1480
VEL30US204-zz-JA-H, VEL30US204-zz-JA, VER30US204-JA, VET30US204C2-JA	20.4	1470
VEL30US205-zz-JA-H, VEL30US205-zz-JA, VER30US205-JA, VET30US205C2-JA	20.5	1460
VEL30US206-zz-JA-H, VEL30US206-zz-JA, VER30US206-JA, VET30US206C2-JA	20.6	1460
VEL30US207-zz-JA-H, VEL30US207-zz-JA, VER30US207-JA, VET30US207C2-JA	20.7	1450
VEL30US208-zz-JA-H, VEL30US208-zz-JA, VER30US208-JA, VET30US208C2-JA	20.8	1440
VEL30US209-zz-JA-H, VEL30US209-zz-JA, VER30US209-JA, VET30US209C2-JA	20.9	1440
VEL30US210-zz-JA-H, VEL30US210-zz-JA, VER30US210-JA, VET30US210C2-JA	21.0	1430
VEL30US211-zz-JA-H, VEL30US211-zz-JA, VER30US211-JA, VET30US211C2-JA	21.1	1420
VEL30US212-zz-JA-H, VEL30US212-zz-JA, VER30US212-JA, VET30US212C2-JA	21.2	1420
VEL30US213-zz-JA-H, VEL30US213-zz-JA, VER30US213-JA, VET30US213C2-JA	21.3	1410
VEL30US214-zz-JA-H, VEL30US214-zz-JA, VER30US214-JA, VET30US214C2-JA	21.4	1400
VEL30US215-zz-JA-H, VEL30US215-zz-JA, VER30US215-JA, VET30US215C2-JA	21.5	1400
VEL30US216-zz-JA-H, VEL30US216-zz-JA, VER30US216-JA, VET30US216C2-JA	21.6	1390
VEL30US217-zz-JA-H, VEL30US217-zz-JA, VER30US217-JA, VET30US217C2-JA	21.7	1380
VEL30US218-zz-JA-H, VEL30US218-zz-JA, VER30US218-JA, VET30US218C2-JA	21.8	1380
VEL30US219-zz-JA-H, VEL30US219-zz-JA, VER30US219-JA, VET30US219C2-JA	21.9	1370
VEL30US220-zz-JA-H, VEL30US220-zz-JA, VER30US220-JA, VET30US220C2-JA	22.0	1360
VEL30US221-zz-JA-H, VEL30US221-zz-JA, VER30US221-JA, VET30US221C2-JA	22.1	1360
VEL30US222-zz-JA-H, VEL30US222-zz-JA, VER30US222-JA, VET30US222C2-JA	22.2	1350
VEL30US223-zz-JA-H, VEL30US223-zz-JA, VER30US223-JA, VET30US223C2-JA	22.3	1350
VEL30US224-zz-JA-H, VEL30US224-zz-JA, VER30US224-JA, VET30US224C2-JA	22.4	1340
VEL30US225-zz-JA-H, VEL30US225-zz-JA, VER30US225-JA, VET30US225C2-JA	22.5	1330
VEL30US226-zz-JA-H, VEL30US226-zz-JA, VER30US226-JA, VET30US226C2-JA	22.6	1330
VEL30US227-zz-JA-H, VEL30US227-zz-JA, VER30US227-JA, VET30US227C2-JA	22.7	1320
VEL30US228-zz-JA-H, VEL30US228-zz-JA, VER30US228-JA, VET30US228C2-JA	22.8	1320

CERTIFICATE
No. Z1A 16 01 65969 171



Product Service

VEL30US229-zz-JA-H, VEL30US229-zz-JA, VER30US229-JA, VET30US229C2-JA	22.9	1310
VEL30US230-zz-JA-H, VEL30US230-zz-JA, VER30US230-JA, VET30US230C2-JA	23.0	1300
VEL30US231-zz-JA-H, VEL30US231-zz-JA, VER30US231-JA, VET30US231C2-JA	23.1	1300
VEL30US232-zz-JA-H, VEL30US232-zz-JA, VER30US232-JA, VET30US232C2-JA	23.2	1290
VEL30US233-zz-JA-H, VEL30US233-zz-JA, VER30US233-JA, VET30US233C2-JA	23.3	1290
VEL30US234-zz-JA-H, VEL30US234-zz-JA, VER30US234-JA, VET30US234C2-JA	23.4	1280
VEL30US235-zz-JA-H, VEL30US235-zz-JA, VER30US235-JA, VET30US235C2-JA	23.5	1280
VEL30US236-zz-JA-H, VEL30US236-zz-JA, VER30US236-JA, VET30US236C2-JA	23.6	1270
VEL30US237-zz-JA-H, VEL30US237-zz-JA, VER30US237-JA, VET30US237C2-JA	23.7	1270
VEL30US238-zz-JA-H, VEL30US238-zz-JA, VER30US238-JA, VET30US238C2-JA	23.8	1260
VEL30US239-zz-JA-H, VEL30US239-zz-JA, VER30US239-JA, VET30US239C2-JA	23.9	1260
VEL30US240-zz-JA-H, VEL30US240-zz-JA, VER30US240-JA, VET30US240C2-JA	24.0	1250
For model: VEL36USxxx-zz-JA-H, VEL36USxxx-zz-JA, VER36USxxx-JA, VET36USxxxC2-JA		
VEL36US120-zz-JA-H, VEL36US120-zz-JA, VER36US120-JA, VET36US120C2-JA	12.0	3000
VEL36US121-zz-JA-H, VEL36US121-zz-JA, VER36US121-JA, VET36US121C2-JA	12.1	2970
VEL36US122-zz-JA-H, VEL36US122-zz-JA, VER36US122-JA, VET36US122C2-JA	12.2	2950
VEL36US123-zz-JA-H, VEL36US123-zz-JA, VER36US123-JA, VET36US123C2-JA	12.3	2920
VEL36US124-zz-JA-H, VEL36US124-zz-JA, VER36US124-JA, VET36US124C2-JA	12.4	2900
VEL36US125-zz-JA-H, VEL36US125-zz-JA, VER36US125-JA, VET36US125C2-JA	12.5	2880
VEL36US126-zz-JA-H, VEL36US126-zz-JA, VER36US126-JA, VET36US126C2-JA	12.6	2850
VEL36US127-zz-JA-H, VEL36US127-zz-JA, VER36US127-JA, VET36US127C2-JA	12.7	2830
VEL36US128-zz-JA-H, VEL36US128-zz-JA, VER36US128-JA, VET36US128C2-JA	12.8	2810
VEL36US129-zz-JA-H, VEL36US129-zz-JA, VER36US129-JA, VET36US129C2-JA	12.9	2790
VEL36US130-zz-JA-H, VEL36US130-zz-JA, VER36US130-JA, VET36US130C2-JA	13.0	2760
VEL36US131-zz-JA-H, VEL36US131-zz-JA, VER36US131-JA, VET36US131C2-JA	13.1	2740
VEL36US132-zz-JA-H, VEL36US132-zz-JA, VER36US132-JA, VET36US132C2-JA	13.2	2720
VEL36US133-zz-JA-H, VEL36US133-zz-JA, VER36US133-JA, VET36US133C2-JA	13.3	2700
VEL36US134-zz-JA-H, VEL36US134-zz-JA, VER36US134-JA, VET36US134C2-JA	13.4	2680

CERTIFICATE
No. Z1A 16 01 65969 171



Product Service

VEL36US135-zz-JA-H, VEL36US135-zz-JA, VER36US135-JA, VET36US135C2-JA	13.5	2660
VEL36US136-zz-JA-H, VEL36US136-zz-JA, VER36US136-JA, VET36US136C2-JA	13.6	2640
VEL36US137-zz-JA-H, VEL36US137-zz-JA, VER36US137-JA, VET36US137C2-JA	13.7	2620
VEL36US138-zz-JA-H, VEL36US138-zz-JA, VER36US138-JA, VET36US138C2-JA	13.8	2600
VEL36US139-zz-JA-H, VEL36US139-zz-JA, VER36US139-JA, VET36US139C2-JA	13.9	2580
VEL36US140-zz-JA-H, VEL36US140-zz-JA, VER36US140-JA, VET36US140C2-JA	14.0	2570
VEL36US141-zz-JA-H, VEL36US141-zz-JA, VER36US141-JA, VET36US141C2-JA	14.1	2550
VEL36US142-zz-JA-H, VEL36US142-zz-JA, VER36US142-JA, VET36US142C2-JA	14.2	2530
VEL36US143-zz-JA-H, VEL36US143-zz-JA, VER36US143-JA, VET36US143C2-JA	14.3	2510
VEL36US144-zz-JA-H, VEL36US144-zz-JA, VER36US144-JA, VET36US144C2-JA	14.4	2500
VEL36US145-zz-JA-H, VEL36US145-zz-JA, VER36US145-JA, VET36US145C2-JA	14.5	2480
VEL36US146-zz-JA-H, VEL36US146-zz-JA, VER36US146-JA, VET36US146C2-JA	14.6	2460
VEL36US147-zz-JA-H, VEL36US147-zz-JA, VER36US147-JA, VET36US147C2-JA	14.7	2440
VEL36US148-zz-JA-H, VEL36US148-zz-JA, VER36US148-JA, VET36US148C2-JA	14.8	2430
VEL36US149-zz-JA-H, VEL36US149-zz-JA, VER36US149-JA, VET36US149C2-JA	14.9	2410
VEL36US150-zz-JA-H, VEL36US150-zz-JA, VER36US150-JA, VET36US150C2-JA	15.0	2400
VEL36US180-zz-JA-H, VEL36US180-zz-JA, VER36US180-JA, VET36US180C2-JA	18.0	2000
VEL36US181-zz-JA-H, VEL36US181-zz-JA, VER36US181-JA, VET36US181C2-JA	18.1	1980
VEL36US182-zz-JA-H, VEL36US182-zz-JA, VER36US182-JA, VET36US182C2-JA	18.2	1970
VEL36US183-zz-JA-H, VEL36US183-zz-JA, VER36US183-JA, VET36US183C2-JA	18.3	1960
VEL36US184-zz-JA-H, VEL36US184-zz-JA, VER36US184-JA, VET36US184C2-JA	18.4	1940
VEL36US185-zz-JA-H, VEL36US185-zz-JA, VER36US185-JA, VET36US185C2-JA	18.5	1940
VEL36US186-zz-JA-H, VEL36US186-zz-JA, VER36US186-JA, VET36US186C2-JA	18.6	1930
VEL36US187-zz-JA-H, VEL36US187-zz-JA, VER36US187-JA, VET36US187C2-JA	18.7	1920
VEL36US188-zz-JA-H, VEL36US188-zz-JA, VER36US188-JA, VET36US188C2-JA	18.8	1910
VEL36US189-zz-JA-H, VEL36US189-zz-JA, VER36US189-JA, VET36US189C2-JA	18.9	1900
VEL36US190-zz-JA-H, VEL36US190-zz-JA, VER36US190-JA, VET36US190C2-JA	19.0	1890
VEL36US191-zz-JA-H, VEL36US191-zz-JA, VER36US191-JA, VET36US191C2-JA	19.1	1880

CERTIFICATE
No. Z1A 16 01 65969 171



Product Service

VEL36US192-zz-JA-H, VEL36US192-zz-JA, VER36US192-JA, VET36US192C2-JA	19.2	1870
VEL36US193-zz-JA-H, VEL36US193-zz-JA, VER36US193-JA, VET36US193C2-JA	19.3	1860
VEL36US194-zz-JA-H, VEL36US194-zz-JA, VER36US194-JA, VET36US194C2-JA	19.4	1850
VEL36US195-zz-JA-H, VEL36US195-zz-JA, VER36US195-JA, VET36US195C2-JA	19.5	1840
VEL36US196-zz-JA-H, VEL36US196-zz-JA, VER36US196-JA, VET36US196C2-JA	19.6	1830
VEL36US197-zz-JA-H, VEL36US197-zz-JA, VER36US197-JA, VET36US197C2-JA	19.7	1820
VEL36US198-zz-JA-H, VEL36US198-zz-JA, VER36US198-JA, VET36US198C2-JA	19.8	1810
VEL36US199-zz-JA-H, VEL36US199-zz-JA, VER36US199-JA, VET36US199C2-JA	19.9	1800
VEL36US200-zz-JA-H, VEL36US200-zz-JA, VER36US200-JA, VET36US200C2-JA	20.0	1800
VEL36US201-zz-JA-H, VEL36US201-zz-JA, VER36US201-JA, VET36US201C2-JA	20.1	1790
VEL36US202-zz-JA-H, VEL36US202-zz-JA, VER36US202-JA, VET36US202C2-JA	20.2	1780
VEL36US203-zz-JA-H, VEL36US203-zz-JA, VER36US203-JA, VET36US203C2-JA	20.3	1770
VEL36US204-zz-JA-H, VEL36US204-zz-JA, VER36US204-JA, VET36US204C2-JA	20.4	1760
VEL36US205-zz-JA-H, VEL36US205-zz-JA, VER36US205-JA, VET36US205C2-JA	20.5	1750
VEL36US206-zz-JA-H, VEL36US206-zz-JA, VER36US206-JA, VET36US206C2-JA	20.6	1730
VEL36US207-zz-JA-H, VEL36US207-zz-JA, VER36US207-JA, VET36US207C2-JA	20.7	1730
VEL36US208-zz-JA-H, VEL36US208-zz-JA, VER36US208-JA, VET36US208C2-JA	20.8	1730
VEL36US209-zz-JA-H, VEL36US209-zz-JA, VER36US209-JA, VET36US209C2-JA	20.9	1720
VEL36US210-zz-JA-H, VEL36US210-zz-JA, VER36US210-JA, VET36US210C2-JA	21.0	1710
VEL36US211-zz-JA-H, VEL36US211-zz-JA, VER36US211-JA, VET36US211C2-JA	21.1	1690
VEL36US212-zz-JA-H, VEL36US212-zz-JA, VER36US212-JA, VET36US212C2-JA	21.2	1690
VEL36US213-zz-JA-H, VEL36US213-zz-JA, VER36US213-JA, VET36US213C2-JA	21.3	1690
VEL36US214-zz-JA-H, VEL36US214-zz-JA, VER36US214-JA, VET36US214C2-JA	21.4	1680
VEL36US215-zz-JA-H, VEL36US215-zz-JA, VER36US215-JA, VET36US215C2-JA	21.5	1670
VEL36US216-zz-JA-H, VEL36US216-zz-JA, VER36US216-JA, VET36US216C2-JA	21.6	1660
VEL36US217-zz-JA-H, VEL36US217-zz-JA, VER36US217-JA, VET36US217C2-JA	21.7	1650
VEL36US218-zz-JA-H, VEL36US218-zz-JA, VER36US218-JA, VET36US218C2-JA	21.8	1650
VEL36US219-zz-JA-H, VEL36US219-zz-JA, VER36US219-JA, VET36US219C2-JA	21.9	1640

CERTIFICATE
No. Z1A 16 01 65969 171



Product Service

VEL36US220-zz-JA-H, VEL36US220-zz-JA, VER36US220-JA, VET36US220C2-JA	22.0	1630
VEL36US221-zz-JA-H, VEL36US221-zz-JA, VER36US221-JA, VET36US221C2-JA	22.1	1620
VEL36US222-zz-JA-H, VEL36US222-zz-JA, VER36US222-JA, VET36US222C2-JA	22.2	1620
VEL36US223-zz-JA-H, VEL36US223-zz-JA, VER36US223-JA, VET36US223C2-JA	22.3	1610
VEL36US224-zz-JA-H, VEL36US224-zz-JA, VER36US224-JA, VET36US224C2-JA	22.4	1600
VEL36US225-zz-JA-H, VEL36US225-zz-JA, VER36US225-JA, VET36US225C2-JA	22.5	1600
VEL36US226-zz-JA-H, VEL36US226-zz-JA, VER36US226-JA, VET36US226C2-JA	22.6	1590
VEL36US227-zz-JA-H, VEL36US227-zz-JA, VER36US227-JA, VET36US227C2-JA	22.7	1580
VEL36US228-zz-JA-H, VEL36US228-zz-JA, VER36US228-JA, VET36US228C2-JA	22.8	1570
VEL36US229-zz-JA-H, VEL36US229-zz-JA, VER36US229-JA, VET36US229C2-JA	22.9	1570
VEL36US230-zz-JA-H, VEL36US230-zz-JA, VER36US230-JA, VET36US230C2-JA	23.0	1560
VEL36US231-zz-JA-H, VEL36US231-zz-JA, VER36US231-JA, VET36US231C2-JA	23.1	1550
VEL36US232-zz-JA-H, VEL36US232-zz-JA, VER36US232-JA, VET36US232C2-JA	23.2	1550
VEL36US233-zz-JA-H, VEL36US233-zz-JA, VER36US233-JA, VET36US233C2-JA	23.3	1540
VEL36US234-zz-JA-H, VEL36US234-zz-JA, VER36US234-JA, VET36US234C2-JA	23.4	1530
VEL36US235-zz-JA-H, VEL36US235-zz-JA, VER36US235-JA, VET36US235C2-JA	23.5	1530
VEL36US236-zz-JA-H, VEL36US236-zz-JA, VER36US236-JA, VET36US236C2-JA	23.6	1520
VEL36US237-zz-JA-H, VEL36US237-zz-JA, VER36US237-JA, VET36US237C2-JA	23.7	1510
VEL36US238-zz-JA-H, VEL36US238-zz-JA, VER36US238-JA, VET36US238C2-JA	23.8	1510
VEL36US239-zz-JA-H, VEL36US239-zz-JA, VER36US239-JA, VET36US239C2-JA	23.9	1500
VEL36US240-zz-JA-H, VEL36US240-zz-JA, VER36US240-JA, VET36US240C2-JA	24.0	1500

Notes:

1. xxx = 090-150, 180-240 denotes rated output voltage from 9.0-15.0V, 18.0-24.0V with step 0.1V;
2. zz = EU, UK denotes different plug type:
 - a. zz= EU, for Europe plug,
 - b. zz= UK, for United Kingdom plug.